



designed to be better.

[Search](#)

Gator Grip Plug, Yellow

D0651

Gator Grip Plug, 2pole 3wire 50amp 250volt Grounding, Yellow

Where to buy

0






Representative image shown.

- [SPECIFICATIONS](#)
- [RESOURCES](#)

features & benefits

- Gator Grip Jaws grab cord tighter as you hand turn the housing.
- Nylon jaws grip securely, but won't damage insulation.
- Self-locking Dardelet Thread holds securely and assures firm clamping.
- Fast wiring -- simply insert stranded conductors into individual wiring chambers and tighten oversized terminal screws.
- Transparent wiring chamber cover allows visual inspection of wiring chambers to assure proper connections.
- Sloped shoulders won't catch or snap.
- Automatic cord centering.
- Brilliant high-visibility yellow.
- Neoprene Dust Seal helps keep out dirt and debris.
- Dead front construction.

Top 5 Resources

-  Plugs & Connectors (Brochure)
-  Commercial & Industrial Products (Brochure)
-  10/3 thru 4/4 AWG Round Cord (.57" to 1.26" Dia.) Type S,SJ,SV (Instruction Sheet No.)

specifications

General Info

- Color: yellow

Listing Agencies/Third Party Information

- CSA Listing Info: No
- CUL Listing No: No
- cU Lus: No
- cU Rus: No
- Federal Spec: Yes
- Fed Spec Number: WC596
- UL Listing No: UL498
- UL Standard: Yes
- U N SPS C: 39121402
- U R: No

Dimensions

- Depth (U S): 3.57"
- Diameter U S: 2.63"

Technical Information

- Volts A C: 250

Buy American Act Compliance


- Country of Origin: MEXICO
- Buy American Act Status: Trade Agreement Act Compliant
-



resources BROCHURE

-  Plugs & ConnectorsPDF (1.93mb)
-  Commercial & Industrial ProductsPDF (3.52mb)

INSTRUCTION SHEET NO.

-  10/3 thru 4/4 AWG Round Cord (.57" to 1.26" Dia.) Type S,SJ,SVPDF (765.58kb)