

Zm91cnRoLWx2bCBjb2wzlj4gPGEgaWQ9ImN0bDA1X01haW50YXYxX2N0bDAYX3JwdENvbW1lcmNpYWxfY3RsMDBfcuB0Q29tbWVyY2lhbFN1Ym1lbnVfY



designed to be better.

Search

## Harmony 3-Way Incandescent Dimmer Switch (White)

D703PW

Harmony Incandescent Single Pole/3-Way Dimmers save energy and extend bulb life by reducing the amount of electricity required to power the lights. Energy consumption reductions of up to 30% are possible. Offered in a wide variety of styles to match the look of previously installed switches and receptacles, P&S Dimmers also allow you to match the light level to the task at hand.

Submit Query

Where to buy

Submit Query

Like 0

Tweet 0

0

Email Print



## product gallery

Representative images shown.

### AVAILABLE OPTIONS



Harmony Incandescent Dimmer, Brown



Harmony Incandescent Dimmer, Black



Harmony Incandescent Dimmer, Gray



Harmony Incandescent Dimmer, Ivory



Harmony Incandescent Dimmer, Light Almond



Harmony Incandescent Dimmer, Nickel



Harmony Incandescent Dimmer, Titanium

- SPECIFICATIONS
- YOU MIGHT LIKE
- RESOURCES

### features & benefits

- Convenient operation -- combines ON/OFF Decorator switch with separate slider for dimming control.
- Green LED glows when OFF to make dimmer easy to find in the dark.
- Constant memory returns lights to previous level after a power failure.
- Sleek, ergonomic P&S Decorator style matches other Decorator devices.
- Higher ratings. Single pole and 3-way operation. Works with standard 3-way switches and wiring.
- Screw-pressure-plate backwire terminals save time, space and money.

### Top 5 Resources

- [Better Living Upgrades \(Brochure\)](#)
- [Decorator Paddle Dimmers \(Sell Sheet\)](#)
- [Residential Lighting Controls \(Brochure\)](#)
- [Harmony Incandescent Dimmers \(Installation Instructions\)](#)

## specifications

### General Info

- Color: White
- Product Series: Harmony
- Type: Incandescent
- Number Of Poles: 1 , 3-way
- Style: Decorator

### Listing Agencies/Third Party Information

- CSA Listing Info: No
- cU Lus: Yes
- Federal Spec: No
- UL Listing No: No
- U N SPS C: 39121502
- U R: No

### Dimensions

- Depth (U S): 1.25"
- Height U S: 4.25"
- Width U S: 1.75"

### Technical Information

- Volts: 120V
- Watts: 700

### Buy American Act Compliance

- Country of Origin: UNITED STATES OF AMERICA
- Buy American Act Status: Buy American Act Compliant



### you might like



### Harmony Fan Speed Control, Brown

DDH16P

[View Details](#)



### Screwless Decorator Openings, Plastic Subplate, One Gang, Brown

SWP26

[View Details](#)



### CornerMate Cord Organizer

[View Details](#)


### resources BROCHURE

- [Better Living UpgradesPDF \(1.2mb\)](#)
- [Residential Lighting ControlsPDF \(264.47kb\)](#)

**SELL SHEET**

 Decorator Paddle DimmersPDF (832.06kb)

**INSTALLATION INSTRUCTIONS**

 Harmony Incandescent DimmersPDF (264.29kb)