

1YkxpbmsilGhyZWY9li93aXJILWNhYmxlLW1hbmFnZW1lbnQvY2FibGUtdHJheS13aXJILW1lc2guYXNweCI+Q2FibGUgVHJheSA1fDpcmUgTWVzaDwvYT4g



designed to be better.

Search

## Tamper-Resistant Floor Box Assembly - One Gang for Wood Sub-Floors

FB1TRDRN

Tamper-Resistant Floor Box Assembly. #8 duplex opening. Two threaded screw plug, Includes 3232 15 amp, 125 volt tamper-resistant receptacle. Nickel.

Submit Query

Where to buy Enter Postal Code

Submit Query

0

Email Print



Representative image shown.

- SPECIFICATIONS
- RESOURCES

### features & benefits

- Tamper-Resistant shutters let plugs in, keep other things out.
- Rugged diecast cover plates.
- Meets UL514(c) and NEC 314.27(c).
- Scrub water compliant.
- With durable nickel or brass cover plates.
- Dual-voltage models available.
- Swing brackets mounting option eliminates drilling tile flooring for mounting screws.
- Wood sub-floors only.
- Wire Fill (AWG): 10 No. 14, 9 No. 12, 8 No. 10.

### Top 5 Resources

- Floor Boxes (Brochure)
- Series Tamper-Resistant Floor Box, FB-1 and FB-2 (Installation Instructions)

### specifications

#### General Info

- Product Series: Slater
- Component Type: Full Assemblies

#### Listing Agencies/Third Party Information

- CSA Listing Info: No
- CUL Listing No: No
- cU Lus: Yes
- cU Rus: No
- Federal Spec: No
- UL Listing No: No
- U N SPS C: 39121308
- U R: No

#### Dimensions

- Depth (U S): 4.0
- Length: 4.75
- Volume: 20.5
- Width U S: 3.25

#### Technical Information


- Material: Nickel
- Floor Type: Wood

**Buy American Act Compliance**


- Country of Origin: UNITED STATES OF AMERICA
- Buy American Act Status: Buy American Act Compliant
- 



**resources**  
**BROCHURE**

 Floor BoxesPDF (925.15kb)

**INSTALLATION INSTRUCTIONS**

 Series Tamper-Resistant Floor Box, FB-1 and FB-2PDF (3.22mb)