



designed to be better.

[Search](#)

Support Grips Standard Duty, Closed Mesh

FC125U

Standard-duty, Closed mesh, Single eye grips. Cable diameter - 1.250-1.490", Bale length - 10", Mesh length - 16", Break Strength - 1,680 lbs.

[Submit Query](#)

Where to buy

[Submit Query](#)

0

[Email](#) [Print](#)



Representative image shown.

- [SPECIFICATIONS](#)
- [RESOURCES](#)

features & benefits

- Standard closed mesh support grips are designed for loads up to 600 lbs.
- Vertical runs of no more than 100 ft.
- They are available in a variety of eye styles and cable ranges for supporting electrical and fiber optic cable, metal rods, and tubing.
- Closed mesh support grips are used when the end of the cable is accessible.
- Support grips are woven of corrosion-resistant tinned-bronze wire.

Top 5 Resources

 [Commercial & Industrial Products \(Brochure\)](#)

specifications

General Info

- Typical Applications: Service Drop
- Product Series: Flexcor
- Type: Closed Mesh
- Duty: Standard Duty
- Special Features: Single Eye

Listing Agencies/Third Party Information

- CSA Listing Info: Yes
- CUL Listing No: No
- cU Lus: No
- cU Rus: No
- Federal Spec: No
- UL Listing No: No
- U N SPS C: 39121722
- U R: No

Dimensions

- Weight: 0.26815

Buy American Act Compliance

- Country of Origin: MEXICO
- Buy American Act Status: Trade Agreement Act Compliant
-



resources

BROCHURE

-  Commercial & Industrial ProductsPDF (3.52mb)