

IGhyZWY9li93aXJILWNhYmxlLW1hbmFnZW1lbnQvcG93ZXItZGlzdHJpYnV0aW9uLmFzcHgiPjxpbWcgcmVwbGFJZT0iZHNyYyYlgZHNyYz0iL34vbWVkaWEvN



designed to be better.

Search

## Support Grips Standard Duty, Closed Mesh

FC150U

Standard-duty, Closed mesh, Single eye grips. Cable Diameter - 1.500-1.740", Bale length - 12", Mesh length - 18", 1,680 lbs.

Submit Query

Where to buy

Enter Postal Code

Submit Query

0



Representative image shown.

- SPECIFICATIONS
- RESOURCES

### features & benefits

- Standard closed mesh support grips are designed for loads up to 600 lbs.
- Vertical runs of no more than 100 ft.
- They are available in a variety of eye styles and cable ranges for supporting electrical and fiber optic cable, metal rods, and tubing.
- Closed mesh support grips are used when the end of the cable is accessible.
- Support grips are woven of corrosion-resistant tinned-bronze wire.

### Top 5 Resources

- Commercial & Industrial Products (Brochure)

### specifications

#### General Info

- Typical Applications: Service Drop
- Product Series: Flexcor
- Type: Closed Mesh
- Duty: Standard Duty
- Special Features: Single Eye

#### Listing Agencies/Third Party Information

- CSA Listing Info: Yes
- CUL Listing No: No
- cU Lus: No
- cU Rus: No
- Federal Spec: No
- UL Listing No: No
- U N SPS C: 39121722
- U R: No

#### Dimensions

- Weight: 0.23522

#### Buy American Act Compliance

- Country of Origin: MEXICO
- Buy American Act Status: Trade Agreement Act Compliant



**RESOURCES**  
**BROCHURE**

 Commercial & Industrial ProductsPDF (3.52mb)