

JzLmFzchGjPIdoaXRlIFBhcGVyczwvYT48L2xpPiA8L3VsPiA8ZGI2IHNoeWxIPSJjbGVhcjogYm90aDsiPjwvZGI2PiA8L2xpPiA8L3VsPiA8L2Rpdj4gPCEtLSAvIG



designed to be better.

Search

Isolated Ground Heavy-Duty Spec Grade Receptacles, Back & Side Wire, 20A, 125V, Gray

IG5362GRY
Isolated Ground Heavy-Duty Spec Grade Duplex Receptacle Back & Side Wire 20amp 125volt Gray

Submit Query Enter Postal Code Submit Query 0



Representative image shown.

AVAILABLE OPTIONS



Isolated Ground Heavy-Duty Spec Grade Receptacles, Back & Side Wire, 20A, 125V, White



Isolated Ground Heavy-Duty Spec Grade Receptacles, Back & Side Wire, 20A, 125V, Orange



Isolated Ground Heavy-Duty Spec Grade Receptacles, Back & Side Wire, 20A, 125V, Black



Isolated Ground Heavy-Duty Spec Grade Receptacles, Back & Side Wire, 20A, 125V, Blue



Isolated Ground Heavy-Duty Spec Grade Receptacles, Back & Side Wire, 20A, 125V, Ivory



Isolated Ground Heavy-Duty Spec Grade Receptacles, Back & Side Wire, 20A, 125V, Light Almond



Isolated Ground Heavy-Duty Spec Grade Receptacles, Back & Side Wire, 20A, 125V, Red

- SPECIFICATIONS
- RESOURCES

features & benefits

- IG symbol and Isolated Ground markings for easy identification and circuit delineation.
- Triple-wipe brass contacts ensure lasting, positive contact with plug blades.
- High-impact resistant nylon face resists impacts and scrapes.
- Corrosion-resistant plated steel strap.
- Patented feature, external screw-pressure-plate back wire clamp on ground terminal for faster, easier installation.
- Plastic barrier isolates grounding terminal from mounting strap and metal boxes.
- Side and internal screw-pressure-plate back wire capability with #14 - #10 AWG copper or copper-clad, solid or stranded wire.
- Auto-ground clip assures positive ground.

Top 5 Resources

- Commercial & Industrial Products (Brochure)
- Heavy Duty Isolated Ground Receptacles, SF1306R1 (Cutsheet)

specifications

General Info

- Color: gray
- Type: Receptacles
- Number Of Poles: 2
- Number Of Wires: 3
- Special Features: Isolated ground,back,side wire
- Style: Duplex

Listing Agencies/Third Party Information

- CSA Listing Info: C22.2 No. 42
- CSA Standard: Yes
- Federal Spec: Yes
- Fed Spec Number: WC596
- UL Listing No: UL498
- UL Standard: Yes
- U N SPS C: 39121406
- U R: No

Dimensions

- Depth (U S): 0.922"
- Height U S: 3.281"
- Width U S: 1.322"

Technical Information

- Amps: 20 Amp
- NEMA Configuration Number: 5-20R
- Volts: 125V
- Volts A C: 125
- Capacity: Duplex
- Grade Type: Federal Specification

Buy American Act Compliance

- Country of Origin: MEXICO
- Buy American Act Status: Trade Agreement Act Compliant



resources

BROCHURE

- Commercial & Industrial ProductsPDF (3.52mb)

CUTSHEET

- Heavy Duty Isolated Ground Receptacles, SF1306R1PDF (186.35kb)

