

RDE5Q0EyQy5hc2h4FgleB09uQ2xpY2sFiwFfZ2FxlN1c2goWydfdHJhY2tFdmVudCcsiCdSZXNvdXJjZXMnLCAAnRG93bmxvYWRIZCcsJ3s1MUM5RTY1Mi0;



designed to be better.

Search

Isolated Ground Heavy-Duty Hospital Grade Receptacles, Back & Side Wire, 20A, 125V, Orange

IG8300
Isolated Ground Heavy-Duty Hospital Grade Duplex Receptacle Back & Side Wire 20amp 125volt Orange

Submit Query
Where to buy Enter Postal Code Submit Query 0 Email Print



Representative image shown.

AVAILABLE OPTIONS



Isolated Ground Heavy-Duty Hospital Grade Receptacles, Back & Side Wire, 20A, 125V, White



Isolated Ground Heavy-Duty Hospital Grade Receptacles, Back & Side Wire, 20A, 125V, Ivory



Isolated Ground Heavy-Duty Hospital Grade Receptacles, Back & Side Wire, 20A, 125V, Light Almond



Isolated Ground Heavy-Duty Hospital Grade Receptacles, Back & Side Wire, 20A, 125V, Red


- SPECIFICATIONS
- RESOURCES

features & benefits

- IG symbol and Isolated Ground markings for easy identification and circuit delineation.
- Triple-wipe brass contacts ensure lasting, positive contact with plug blades.
- High-impact resistant nylon face resists impacts and scrapes.
- Corrosion-resistant plated steel strap.
- Patented feature, external screw-pressure-plate back wire clamp on ground terminal for faster, easier installation.

- Plastic barrier isolates grounding terminal from mounting strap and metal boxes.
- Side and internal screw-pressure-plate back wire capability with #14 - #10 AWG copper or copper-clad, solid or stranded wire.
- Auto-ground clip assures positive ground.

Top 5 Resources

-  [Hospital Grade Heavy Duty Isolated Ground Receptacles, SF712R1 \(Cutsheet\)](#)

specifications

General Info

- Color: orange
- Type: Receptacles
- Number Of Poles: 2
- Number Of Wires: 3
- Special Features: Isolated Ground,back,side wire
- Style: Duplex

Listing Agencies/Third Party Information

- CSA Listing Info: C22.2 No. 42
- CSA Standard: Yes
- Federal Spec: Yes
- Fed Spec Number: WC596
- UL Listing No: UL498
- UL Standard: Yes
- U N SPS C: 39121406
- U R: No

Dimensions

- Depth (U S): .922"
- Height U S: 3.281"
- Width U S: 1.322"

Technical Information

- Amps: 20 Amp
- NEMA Configuration Number: 5-20R
- Volts: 125V
- Volts A C: 125
- Capacity: Duplex
- Grade Type: Hospital,Federal Specification

Buy American Act Compliance

- Country of Origin: MEXICO
- Buy American Act Status: Trade Agreement Act Compliant
-



resources CUTSHEET

-  [Hospital Grade Heavy Duty Isolated Ground Receptacles, SF712R1PDF \(340.44kb\)](#)