

glfAAUOV2lyZWQgTmV0d29ya3NkAgMPDxYCHwQFH9uZXR3b3JraW5nL3dpcmVklW5ldHdvcmtzLmFzcHhkFgJmDxYCHwAFEjxpbWcgcmVwbGFjZT0iZH



designed to be better.

Search

# 30 Amp NEMA L1030 Connector - Black Back, White Front Body

L1030C

Turnlok Connector 3wire 30amp 125/250v

Submit Query

Where to buy Enter Postal Code

Submit Query

0

Email Print



Representative image shown.

- SPECIFICATIONS
- RESOURCES

## features & benefits

- Quick-thread assembly screws and cord-grip screws come backed-out, ready-to-wire.
- Industrial-strength, brass alloy plug blades and connector contacts resist heat rise, provide excellent conductivity.
- Raised ribs provide non-slip gripping profile for turning to lock and unlock.
- Double dovetail design provides superior protection against cord pull-out forces.
- Impact- and corrosion-resistant durable nylon 6/6 shell material.
- Rounded back contour reduces snags and hang-ups on the job site.
- Scallop shell design provides non-slip gripping surface for insertion and withdrawal.
- Visible stamped NEMA configuration and device rating.
- New-design external cord grips provide visible assurance of safe and proper cord retention.
- Integral flexible rubber cord grommet conforms to and seals around SO cord to provide protection from oils, water, or chips entering wiring chamber.

## Top 5 Resources

Commercial & Industrial Products (Brochure)

## specifications

### General Info

- Color: Black, White
- Type: Connector
- Number Of Wires: 3

### Listing Agencies/Third Party Information

- CSA Listing Info: No
- CUL Listing No: No
- Federal Spec: Yes
- Fed Spec Number: WC596
- UL Listing No: 498
- UL Standard: Yes
- U N SPS C: 39121403

### Dimensions

- Length: 3.33"
- Width U S: 2.20"

### Technical Information

- Amps: 30 Amp
- NEMA Configuration Number: L1030
- Volts: 125/250V
- Volts A C: 125/250

### Buy American Act Compliance

- Country of Origin: MEXICO

- Buy American Act Status: Trade Agreement Act Compliant



**resources**  
**BROCHURE**

 Commercial & Industrial ProductsPDF (3.52mb)