

NwYW4+IDwvZGI2PiA8IS0tIGl0ZW0taW1hZ2UgLS0+IDxwPjxhIGlkPSJjdGwwNV9NYWluTmF2MV9jdGwwMI9ycHROZXdJdGVtc19jdGwwM19obE5ld0xpbms



designed to be better.

[Search](#)

30 Amp NEMA L1130 Single Receptacle

L1130R

Turnlok Receptacle 3wire 30amp 3phase 250v

[Submit Query](#)

Where to buy

[Submit Query](#)

0



Representative image shown.

- [SPECIFICATIONS](#)
- [RESOURCES](#)

features & benefits

- Compact, impact-resistant nylon face and body are ultrasonically welded together for unrivaled strength.
- Face color coding by voltage facilitates locating and mating of proper devices.
- One piece, high-grade brass contacts offer excellent conductivity and heat-rise resistance.
- Clearly marked NEMA configuration, rating, and third-party listing on each unit's face.
- Single-piece, solid brass mounting strap is free of easily loosened rivets found on other brands.
- Side and external screw-pressure-plate back wire capability.
- Accepts #14 - #10 AWG.

Top 5 Resources

- [Commercial & Industrial Products \(Brochure\)](#)

specifications

General Info

- Type: Single, Receptacles
- Number Of Wires: 3

Listing Agencies/Third Party Information

- CSA Listing Info: No
- CUL Listing No: No
- cU Rus: No
- Federal Spec: Yes
- Fed Spec Number: WC596
- UL Listing No: 498
- UL Standard: Yes
- U N SPS C: 39121403
- U R: No

Dimensions

- Depth (U S): 1.28"
- Height U S: 3.28"
- Width U S: 1.61"

Technical Information

- Amps: 30 Amp
- NEMA Configuration Number: L1130
- Volts: 250V
- Volts A C: 250

Buy American Act Compliance

- Country of Origin: MEXICO
- Buy American Act Status: Trade Agreement Act Compliant



resources
BROCHURE

 Commercial & Industrial ProductsPDF (3.52mb)