



designed to be better.

[Search](#)

20 Amp NEMA L1420 Inlet, Gray

L1420FI

Flanged Inlet 4wire 20amp 125/250volt Turnlok

[Submit Query](#)

Where to buy

[Submit Query](#)

0

[Email](#) [Print](#)



Representative image shown.

- [SPECIFICATIONS](#)
- [RESOURCES](#)

features & benefits

- Interior components constructed of high-grade brass material for physical and electrical integrity.
- High-impact thermoplastic housing withstands on-the-job abuse.
- Ratings and NEMA configurations are clearly visible on flange face, for fast I.D. while in use.

Top 5 Resources

- [Commercial & Industrial Products \(Brochure\)](#)
- [Plugs & Connectors \(Brochure\)](#)

specifications

General Info

- Color: Gray
- Type: Inlet
- Number Of Wires: 4

Listing Agencies/Third Party Information

- CSA Standard: Yes
- Federal Spec: No
- UL Listing No: 498
- UL Standard: Yes
- U N SPS C: 39121403

Dimensions

- Depth (U S): 1.65"
- Diameter U S: 2.87"

Technical Information



- Amps: 20 Amp
- NEMA Configuration Number: L1420
- Volts: 125/250V
- Volts A C: 125/250

Buy American Act Compliance

- Country of Origin: MEXICO
- Buy American Act Status: Trade Agreement Act Compliant
-



resources BROCHURE

-  Commercial & Industrial ProductsPDF (3.52mb)
-  Plugs & ConnectorsPDF (1.93mb)