



designed to be better.

[Search](#)

20 Amp NEMA L1520 Single Receptacle

L1520R

Turnlok Single Receptacle 4wire 20amp 3phase 250v

[Submit Query](#)

Where to buy

[Submit Query](#)

0

[Email](#) [Print](#)



Representative image shown.

- [SPECIFICATIONS](#)
- [RESOURCES](#)

features & benefits

- Compact, impact-resistant nylon face and body are ultrasonically welded together for unrivaled strength.
- Face color coding by voltage facilitates locating and mating of proper devices.
- One piece, high-grade brass contacts offer excellent conductivity and heat-rise resistance.
- Clearly marked NEMA configuration, rating, and third-party listing on each unit's face.
- Single-piece, solid brass mounting strap is free of easily loosened rivets found on other brands.
- Side and external screw-pressure-plate back wire capability.
- Accepts #14 - #10 AWG.

Top 5 Resources

 [Commercial & Industrial Products \(Brochure\)](#)

specifications

General Info

- Type: Single, Receptacles
- Number Of Wires: 4

Listing Agencies/Third Party Information

- CSA Standard: Yes
- Federal Spec: Yes
- Fed Spec Number: WC596
- UL Listing No: 498
- UL Standard: Yes
- U N SPS C: 39121403

Dimensions

- Depth (U S): 1.19"
- Length: 3.28"
- Width U S: 1.61"

Technical Information

- Amps: 20 Amp
- NEMA Configuration Number: L1520
- Volts: 250V
- Volts A C: 250

Buy American Act Compliance

- Country of Origin: MEXICO
- Buy American Act Status: Trade Agreement Act Compliant
-



resources BROCHURE

 [Commercial & Industrial ProductsPDF \(3.52mb\)](#)