



designed to be better.

Search

# 30 Amp NEMA L1630 Plug - Black Back, White Front Body

L1630P

Turnlok Plug 4wire 30amp 3phase 480v

Submit Query

Where to buy  Enter Postal Code

Submit Query

0

Email Print



Representative image shown.

- SPECIFICATIONS
- RESOURCES

## features & benefits

- Quick-thread assembly screws and cord-grip screws come backed-out, ready-to-wire.
- Industrial-strength, brass alloy plug blades and connector contacts resist heat rise, provide excellent conductivity.
- Raised ribs provide non-slip gripping profile for turning to lock and unlock.
- Double dovetail design provides superior protection against cord pull-out forces.
- Impact- and corrosion-resistant durable nylon 6/6 shell material.
- Rounded back contour reduces snags and hang-ups on the job site.
- Scallop shell design provides non-slip gripping surface for insertion and withdrawal.
- Visible stamped NEMA configuration and device rating.
- New-design external cord grips provide visible assurance of safe and proper cord retention.
- Integral flexible rubber cord grommet conforms to and seals around SO cord to provide protection from oils, water, or chips entering wiring chamber.

## Top 5 Resources

 Turnlok EHU Plugs & Connectors 4 Wire, SF1704R1 (Cutsheet)

## specifications

### General Info

- Color: Black, White
- Type: Plug
- Number Of Wires: 4

### Listing Agencies/Third Party Information

- CSA Standard: Yes
- Federal Spec: Yes
- Fed Spec Number: WC596
- UL Listing No: 498
- UL Standard: Yes
- U N SPS C: 39121403

### Dimensions

- Diameter U S: 2.20"
- Length: 3.75"

### Technical Information

- Amps: 30 Amp
- NEMA Configuration Number: L1630
- Volts: 480V
- Volts A C: 480

### Buy American Act Compliance

- Country of Origin: MEXICO
- Buy American Act Status: Trade Agreement Act Compliant
- 



## resources

### CUTSHEET

 Turnlok EHU Plugs & Connectors 4 Wire, SF1704R1PDF (552.93kb)