

jPSivfi9tZWRpYS8zOUVDMklwMjNFRTM0NDEwQTcwQTFFREQ4OTU4MjdFRS5hc2h4IiBhbHQ9IldpcmVsZXNzIE5ldHdvcmtzIiB3aWR0aD0iMjE4IiBoZWlna



designed to be better.

Search

30 Amp NEMA L1630 Single Receptacle

L1630R

Turnlok Single Receptacle 4wire 30amp 3phase 480v

Submit Query

Where to buy Enter Postal Code

Submit Query

0

Email Print



Representative image shown.

- SPECIFICATIONS
- RESOURCES

features & benefits

- Compact, impact-resistant nylon face and body are ultrasonically welded together for unrivaled strength.
- Face color coding by voltage facilitates locating and mating of proper devices.
- One piece, high-grade brass contacts offer excellent conductivity and heat-rise resistance.
- Clearly marked NEMA configuration, rating, and third-party listing on each unit's face.
- Single-piece, solid brass mounting strap is free of easily loosened rivets found on other brands.
- Side and external screw-pressure-plate back wire capability.
- Accepts #14 - #10 AWG.

Top 5 Resources

- Commercial & Industrial Products (Brochure)

specifications

General Info

- Type: Single, Receptacles
- Number Of Wires: 4

Listing Agencies/Third Party Information

- CSA Standard: Yes
- Federal Spec: Yes
- Fed Spec Number: WC596
- UL Listing No: 498
- UL Standard: Yes
- U N SPS C: 39121403

Dimensions

- Depth (U S): 1.28"
- Height U S: 3.28"
- Width U S: 1.61"

Technical Information


- Amps: 30 Amp
- NEMA Configuration Number: L1630
- Volts: 480V
- Volts A C: 480

Buy American Act Compliance

- Country of Origin: MEXICO
- Buy American Act Status: Trade Agreement Act Compliant



resources
BROCHURE

 Commercial & Industrial ProductsPDF (3.52mb)