

NFUgZmliZXIgy2FiaW5ldCwgMTkylGZpYmVylGNhcGFjaXR5PC9hPjwvcD4gPC9saT4gPGxpPjwhLS0gSXRlbUxpjbms6TmF2aWdhYmxlVGI0bGUuLS0+IDxk



designed to be better.

Search

## 20 Amp NEMA L1820 Single Receptacle

L1820R

Receptacle Single 4wire 20amp 120/208volt Turnlok

Submit Query

Where to buy Enter Postal Code

Submit Query

0

Email Print



Representative image shown.

- SPECIFICATIONS
- RESOURCES

### features & benefits

- Compact, impact-resistant nylon face and body are ultrasonically welded together for unrivaled strength.
- Face color coding by voltage facilitates locating and mating of proper devices.
- One piece, high-grade brass contacts offer excellent conductivity and heat-rise resistance.
- Clearly marked NEMA configuration, rating, and third-party listing on each unit's face.
- Single-piece, solid brass mounting strap is free of easily loosened rivets found on other brands.
- Side and external screw-pressure-plate back wire capability.
- Accepts #14 - #10 AWG.

### Top 5 Resources

- Commercial & Industrial Products (Brochure)

### specifications

#### General Info

- Type: Single, Receptacles
- Number Of Wires: 4

#### Listing Agencies/Third Party Information

- Federal Spec: Yes
- Fed Spec Number: WC596
- UL Listing No: 498
- UL Standard: Yes
- U N SPS C: 39121403

#### Dimensions

- Depth (U S): 1.19"
- Length: 3.28"
- Width U S: 1.61"

#### Technical Information


- Amps: 20 Amp
- NEMA Configuration Number: L1820
- Volts: 120/280V
- Volts A C: 120/280

#### Buy American Act Compliance

- Country of Origin: MEXICO
- Buy American Act Status: Trade Agreement Act Compliant



**resources**  
**BROCHURE**

 Commercial & Industrial ProductsPDF (3.52mb)