

ZWlnaHQ9ljExMilgZ5kAgUPDxYCHwQFHi9hdWRpby12aWRlby9ob21lLXRoZWZ0ZXluYXNweGQWAglBDxYCHwAFDEhvbWUgVGhYXRlcmQCBg9kFgYC



designed to be better.

[Search](#)

30 Amp L2130 Single Receptacle

L2130R

Turnlok Single Receptacle 5wire 30amp 3phase 120/208v

[Submit Query](#)

Where to buy

[Submit Query](#)

0



Representative image shown.

- SPECIFICATIONS
- RESOURCES

features & benefits

- Compact, impact-resistant nylon face and body are ultrasonically welded together for unrivaled strength.
- Face color coding by voltage facilitates locating and mating of proper devices.
- One piece, high-grade brass contacts offer excellent conductivity and heat-rise resistance.
- Clearly marked NEMA configuration, rating, and third-party listing on each unit's face.
- Single-piece, solid brass mounting strap is free of easily loosened rivets found on other brands.
- Side and external screw-pressure-plate back wire capability.
- Accepts #14 - #10 AWG.

Top 5 Resources

- [Commercial & Industrial Products \(Brochure\)](#)

specifications

General Info

- Type: Single, Receptacles
- Number Of Wires: 5

Listing Agencies/Third Party Information

- CSA Standard: Yes
- Federal Spec: Yes
- Fed Spec Number: WC596
- UL Listing No: 498
- UL Standard: Yes
- U N SPS C: 39121403

Dimensions

- Depth (U S): 1.28"
- Height U S: 3.28"
- Width U S: 1.61"

Technical Information

- Amps: 30 Amp
- NEMA Configuration Number: L2130
- Volts: 120/208V
- Volts A C: 120/208

Buy American Act Compliance

- Country of Origin: MEXICO
- Buy American Act Status: Trade Agreement Act Compliant



resources
BROCHURE

 Commercial & Industrial ProductsPDF (3.52mb)