

hc3M9ImNvbDliPiA8YSBpZD0iY3RsMDVftWFpbk5hdjFFY3RsMDJfcnB0Q29tbWVvY2lhbF9jdGwwM19ycHRDb21tZXJjaWFsU3VibWVudV9jdGwxMI9obENvt



designed to be better.

Search

## 20 Amp NEMA L520 Single Receptacle

L520R

Turnlok Receptacle Single 3wire 20amp 125v

Submit Query

Where to buy

Submit Query

0



Representative image shown.

- SPECIFICATIONS
- RESOURCES

### features & benefits

- Compact, impact-resistant nylon face and body are ultrasonically welded together for unrivaled strength.
- Face color coding by voltage facilitates locating and mating of proper devices.
- One piece, high-grade brass contacts offer excellent conductivity and heat-rise resistance.
- Clearly marked NEMA configuration, rating, and third-party listing on each unit's face.
- Single-piece, solid brass mounting strap is free of easily loosened rivets found on other brands.
- Side and external screw-pressure-plate back wire capability.
- Accepts #14 - #10 AWG.

### Top 5 Resources

- Commercial & Industrial Products (Brochure)
- Turnlok Heavy Duty Receptacles, SF1701R1 (Cutsheet)

### specifications

#### General Info

- Type: Single, Receptacles
- Number Of Wires: 3

#### Listing Agencies/Third Party Information

- CSA Listing Info: No
- CUL Listing No: No
- cU Lus: Yes
- cU Rus: No
- Federal Spec: Yes
- Fed Spec Number: WC596
- UL Listing No: No
- U N SPS C: 39121403
- U R: No

#### Dimensions

- Depth (U S): 1.19"
- Height U S: 3.28"
- Width U S: 1.61"

#### Technical Information

- Amps: 20 Amp
- NEMA Configuration Number: L520
- Volts: 125V
- Volts A C: 125

#### Buy American Act Compliance

- Country of Origin: MEXICO

- Buy American Act Status: Trade Agreement Act Compliant



**resources**  
**BROCHURE**

 Commercial & Industrial ProductsPDF (3.52mb)

**CUTSHEET**

 Turnlok Heavy Duty Receptacles, SF1701R1PDF (235.57kb)