

OUFENDkzOTg1Rjc3NjRCODdFNDJDNEEuYXNoeClgYWx0PSJBVjBDb25uZWNoaXZpdHkiIHdpZHRoPSlyMTgilGhlaWdodD0iMTEyIiAvPjwvYT4gPGEgaW



designed to be better.

Search

30 Amp NEMA L530 Single Receptacle

L530R

Turnlok Receptacle Single 3wire 30amp 125v

Submit Query

Where to buy

Submit Query

0



Representative image shown.

- SPECIFICATIONS
- RESOURCES

features & benefits

- Compact, impact-resistant nylon face and body are ultrasonically welded together for unrivaled strength.
- Face color coding by voltage facilitates locating and mating of proper devices.
- One piece, high-grade brass contacts offer excellent conductivity and heat-rise resistance.
- Clearly marked NEMA configuration, rating, and third-party listing on each unit's face.
- Single-piece, solid brass mounting strap is free of easily loosened rivets found on other brands.
- Side and external screw-pressure-plate back wire capability.
- Accepts #14 - #10 AWG.

Top 5 Resources

- Commercial & Industrial Products (Brochure)
- Turnlok Heavy Duty Receptacles, SF1701R1 (Cutsheet)

specifications

General Info

- Type: Single, Receptacles
- Number Of Wires: 3

Listing Agencies/Third Party Information

- CSA Standard: Yes
- CUL Listing No: No
- cU Rus: No
- Federal Spec: Yes
- Fed Spec Number: WC596
- UL Listing No: 498
- UL Standard: Yes
- U N SPS C: 39121403
- U R: No

Dimensions

- Depth (U S): 1.28"
- Height U S: 3.28"
- Width U S: 1.62"

Technical Information

- Amps: 30 Amp
- NEMA Configuration Number: L530
- Volts: 125V
- Volts A C: 125

Buy American Act Compliance

- Country of Origin: MEXICO

- Buy American Act Status: Trade Agreement Act Compliant



resources
BROCHURE

 [Commercial & Industrial ProductsPDF \(3.52mb\)](#)

CUTSHEET

 [Turnlok Heavy Duty Receptacles, SF1701R1PDF \(235.57kb\)](#)