

1hdXRvbWF0aW9uL3VzZXItaW50ZXJmYWNLcy5hc3B4ZBYCZg8WAh8ABXs8aW1nIHJlcGxhY2U9ImRzcmMlIGRzcmM9li9+L21IZGhL0FDRtKyQjg0MTczN'



designed to be better.

Search

30 Amp NEMA L630 Flanged Inlet, Gray

L630FI

Turnlok Flanged Inlet, 3wire 30amp 250volt, Gray

Submit Query

Where to buy

Enter Postal Code

Submit Query

0



Representative image shown.

- SPECIFICATIONS
- RESOURCES

features & benefits

- Interior components constructed of high-grade brass material for physical and electrical integrity.
- High-impact thermoplastic housing withstands on-the-job abuse.
- Ratings and NEMA configurations are clearly visible on flange face, for fast I.D. while in use.

Top 5 Resources

- Commercial & Industrial Products (Brochure)
- Plugs & Connectors (Brochure)
- Turnlok Heavy Duty Flanged Inlets & Outlets, SF1703R1 (Cutsheet)

specifications

General Info

- Color: Gray
- Type: Flanged Inlet
- Number Of Wires: 3

Listing Agencies/Third Party Information

- CSA Standard: Yes
- CUL Listing No: No
- cU Lus: No
- cU Rus: No
- Federal Spec: No
- UL Listing No: 498
- UL Standard: Yes
- U N SPS C: 39121403
- U R: No

Dimensions

- Depth (U S): 1.750"
- Diameter U S: 3.12"

Technical Information



- Amps: 30 Amp
- NEMA Configuration Number: L630
- Volts: 250V
- Volts A C: 250

Buy American Act Compliance

- Country of Origin: MEXICO
- Buy American Act Status: Trade Agreement Act Compliant



resources
BROCHURE

-  [Commercial & Industrial ProductsPDF \(3.52mb\)](#)
-  [Plugs & ConnectorsPDF \(1.93mb\)](#)

CUTSHEET

-  [Turnlok Heavy Duty Flanged Inlets & Outlets, SF1703R1PDF \(189.27kb\)](#)