



designed to be better.

[Search](#)

20 Amp NEMA L720 Single Receptacle

L720R

Receptacle Single 3wire 20amp 277volt Turnlok

[Submit Query](#)

Where to buy

[Submit Query](#)

0

[Email](#) [Print](#)



Representative image shown.

- [SPECIFICATIONS](#)
- [RESOURCES](#)

features & benefits

- Compact, impact-resistant nylon face and body are ultrasonically welded together for unrivaled strength.
- Face color coding by voltage facilitates locating and mating of proper devices.
- One piece, high-grade brass contacts offer excellent conductivity and heat-rise resistance.
- Clearly marked NEMA configuration, rating, and third-party listing on each unit's face.
- Single-piece, solid brass mounting strap is free of easily loosened rivets found on other brands.
- Side and external screw-pressure-plate back wire capability.
- Accepts #14 - #10 AWG.

Top 5 Resources

- [Commercial & Industrial Products \(Brochure\)](#)
- [Turnlok Heavy Duty Receptacles, SF1701R1 \(Cutsheet\)](#)

specifications

General Info

- Type: Single, Receptacles
- Number Of Wires: 3

Listing Agencies/Third Party Information

- CSA Standard: Yes
- CUL Listing No: No
- cU Lus: No
- cU Rus: No
- Federal Spec: Yes
- Fed Spec Number: WC596
- UL Listing No: 498
- UL Standard: Yes
- U N SPS C: 39121403
- U R: No

Dimensions

- Depth (U S): 1.19"
- Height U S: 3.28"
- Width U S: 1.61"

Technical Information

- Amps: 20 Amp
- NEMA Configuration Number: L720
- Volts: 277V
- Volts A C: 277

Buy American Act Compliance

- Country of Origin: MEXICO
- Buy American Act Status: Trade Agreement Act Compliant
-



resources

BROCHURE

 Commercial & Industrial ProductsPDF (3.52mb)

CUTSHEET

 Turnlok Heavy Duty Receptacles, SF1701R1PDF (235.57kb)