



designed to be better.

[Search](#)

# Industrial Extra Heavy-Duty Specification Grade Switch, Lighted When On, Back & Side Wire, Red

PS15AC1RPL

1pole Pilot Lighted Switch, Back & Side Wire, 15amp 120volt, Red

[Submit Query](#)

Where to buy

[Submit Query](#)

0

[Email](#) [Print](#)



Representative image shown.


- [SPECIFICATIONS](#)
- [RESOURCES](#)

## features & benefits

- External screw-pressure-plate back and side wired. Accepts #14 - #10 AWG copper or copper-clad conductors.
- Heavy-gauge one-piece copper alloy contact arm virtually eliminates contact bounce.
- Cam controls fast "make" and positive "break" to minimize arcing.
- Heavy-duty bumper pads for quiet operation.
- High strength thermoplastic polycarbonate toggle.
- Back body made of glass-reinforced nylon.
- Locking support provides resistance to face and back body separation.
- Oversized silver alloy contacts for long life and better heat dissipation.

- Grounding terminal is standard.
- Shallow design for ease of installation.
- Strap nickel-plated steel with integral ground.
- Auto-ground clip assures positive ground.

## Top 5 Resources

-  Commercial & Industrial Products (Brochure)
-  Extra Heavy-Duty Lighted Switches, SF102R2 (Cutsheet)

## specifications

### General Info

- Color: Red
- Type: Pilot Lighted
- Duty: Extra Heavy Duty
- Number Of Poles: 1

## Listing Agencies/Third Party Information

- CSA Listing Info: C22.2 111
- CSA Standard: Yes
- Federal Spec: Yes
- Fed Spec Number: WS896
- UL Listing No: 20
- UL Standard: Yes
- U N SPS C: 39121507

## Dimensions

- Depth (U S): 1.073"
- Height U S: 3.281"
- Width U S: 1.320"

## Technical Information

- Amps: 15 Amp
- Volts: 120VAC
- Volts A C: 120
- Grade Type: Industrial

## Buy American Act Compliance

- Country of Origin: MEXICO
- Buy American Act Status: Trade Agreement Act Compliant
- 



## resources

### BROCHURE

-  Commercial & Industrial ProductsPDF (3.52mb)

## CUTSHEET

 Extra Heavy-Duty Lighted Switches, SF102R2PDF (273.91kb)