

2N0bDaxX3JwdFJlc2lkZW50aWFsX2N0bDAzX3JwdFJlc2lkZW50aWFsU3VibWVudV9jdGwwMI9obFJlc2lkZW50aWFsU3VITGluyYlgaHJlZj0lL2RpbW1lcnMtc:



designed to be better.

Search

Extra Heavy-Duty Spec. Grade & Security Switches

PS20AC1KL

1pole Key Lock Back & Side Wire 20amp 120/277volt

Submit Query

Where to buy Enter Postal Code

Submit Query

0

Email Print



Representative image shown.

- SPECIFICATIONS
- RESOURCES

features & benefits

Back and side wired. Accepts #14 - #10 AWG. Operated by cam lock for maximum security in critical areas. Recommended for tamper-proof installation in schools, public housing, trailer parks, freight yards, etc. Uses same key as Cat.# 4600 cast enclosure. Key can be removed in both positions.

Top 5 Resources

- Commercial & Industrial Products (Brochure)
- Extra Heavy-Duty Security Switches, SF103R2 (Cutsheet)

specifications

General Info

- Type: Security Switches
- Duty: Extra Heavy Duty
- Number Of Poles: 1

Listing Agencies/Third Party Information

- CSA Listing Info: C22.2 111
- CSA Standard: Yes
- Federal Spec: Yes
- Fed Spec Number: WS896
- UL Listing No: 20
- UL Standard: Yes
- U N SPS C: 39121507

Dimensions

- Depth (U S): 1.073"
- Height U S: 3.281"
- Width U S: 1.320"

Technical Information

- Amps: 20 Amp
- Volts: 120/277VAC
- Volts A C: 120/277
- Grade Type: Specification

Buy American Act Compliance

- Country of Origin: MEXICO
- Buy American Act Status: Trade Agreement Act Compliant



resources
BROCHURE

 [Commercial & Industrial ProductsPDF \(3.52mb\)](#)

CUTSHEET

 [Extra Heavy-Duty Security Switches, SF103R2PDF \(268.64kb\)](#)