



designed to be better.

[Search](#)

Extra Heavy-Duty Spec. Grade & Security Switches

PS20AC2KL

2pole Key Lock Back & Side Wire 20amp 120/277volt

[Submit Query](#)

Where to buy

[Submit Query](#)

0

[Email](#) [Print](#)



Representative image shown.

- [SPECIFICATIONS](#)
- [RESOURCES](#)

features & benefits

Back and side wired. Accepts #14 - #10 AWG. Operated by cam lock for maximum security in critical areas. Recommended for tamper-proof installation in schools, public housing, trailer parks, freight yards, etc. Uses same key as Cat.# 4600 cast enclosure. Key can be removed in both positions.

Top 5 Resources

- [Commercial & Industrial Products \(Brochure\)](#)
- [Extra Heavy-Duty Security Switches, SF103R2 \(Cutsheet\)](#)

specifications

General Info

- Type: Security Switches
- Duty: Extra Heavy Duty
- Number Of Poles: 2

Listing Agencies/Third Party Information

- CSA Listing Info: C22.2 55
- CSA Standard: Yes
- Federal Spec: Yes
- Fed Spec Number: WS896
- UL Listing No: 20
- UL Standard: Yes
- U N SPS C: 39121507

Dimensions

- Depth (U S): 1.073"
- Height U S: 3.281"
- Width U S: 1.320"

Technical Information

- Amps: 20 Amp
- Volts: 120/277VAC
- Volts A C: 120/277
- Grade Type: Specification

Buy American Act Compliance

- Country of Origin: MEXICO
- Buy American Act Status: Trade Agreement Act Compliant
-



resources BROCHURE

 Commercial & Industrial ProductsPDF (3.52mb)

CUTSHEET

 Extra Heavy-Duty Security Switches, SF103R2PDF (268.64kb)