



designed to be better.

Search

# Industrial Extra Heavy-Duty Specification Grade Lock Switch Back & Side Wire, Gray

PS20AC3L

3way Lock Switch, Back & Side Wire, 20amp 120/277volt, Gray (Key can be removed in both positions)

Submit Query

Where to buy Enter Postal Code

Submit Query

0

Email Print



Representative image shown.

## AVAILABLE OPTIONS



Industrial Extra Heavy-Duty Specification Grade Lock Switch Back & Side Wire, White



Industrial Extra Heavy-Duty Specification Grade Lock Switch Back & Side Wire, Ivory



Industrial Extra Heavy-Duty Specification Grade Lock Switch Back & Side Wire, Light Almond



Industrial Extra Heavy-Duty Specification Grade Lock Switch Back & Side Wire, Red

- SPECIFICATIONS
- RESOURCES

## features & benefits

- External screw-pressure-plate back and side wired. Accepts #14 - #10 AWG copper or copper-clad conductors.
- Heavy-gauge one-piece copper alloy contact arm virtually eliminates contact bounce.
- Cam controls fast "make" and positive "break" to minimize arcing.
- Heavy-duty bumper pads for quiet operation.
- High strength thermoplastic polycarbonate toggle.
- Back body made of glass-reinforced nylon.
- Locking support provides resistance to face and back body separation.
- Oversized silver alloy contacts for long life and better heat dissipation.
- Grounding terminal is standard.
- Shallow design for ease of installation.
- Strap nickel-plated steel with integral ground.
- Auto-ground clip assures positive ground.

## Top 5 Resources

-  [Commercial & Industrial Products \(Brochure\)](#)
-  [Extra Heavy-Duty Locking Switches, SF106R2 \(Cutsheet\)](#)

## specifications

### General Info

- Color: Gray

- Type: Lock Key
- Duty: Extra Heavy Duty
- Number Of Poles: 3-way

### Listing Agencies/Third Party Information

- CSA Listing Info: C22.2 111
- CSA Standard: Yes
- Federal Spec: Yes
- Fed Spec Number: WS896
- UL Listing No: 20
- UL Standard: Yes
- U N SPS C: 39121507

### Dimensions

- Depth (U S): 1.073"
- Height U S: 3.281"
- Width U S: 1.320"

### Technical Information

- Amps: 20 Amp
- Volts: 120/277VAC
- Volts A C: 120/277
- Grade Type: Industrial

### Buy American Act Compliance

- Country of Origin: MEXICO
- Buy American Act Status: Trade Agreement Act Compliant
- 



### resources BROCHURE

 Commercial & Industrial ProductsPDF (3.52mb)

### CUTSHEET

 Extra Heavy-Duty Locking Switches, SF106R2PDF (268.53kb)