

X2N0bDA5X2hsUmVzaWRlbnRpYWxMaW5rliBjbGFzc0iaGikZS1uZXcilGhyZWY9li9uZXR3b3JraW5nLmFzcHgiPkhvbWUgTmV0d29ya2luZzwwYT4gPHVsIG



designed to be better.

Search

Non-Fusible Safety Switch

PS30SS

Non-Fusible Safety Switch. 30 amp, 600 vac.

Submit Query

Where to buy Enter Postal Code Submit Query 0

Email Print



Representative image shown.

- SPECIFICATIONS
- RESOURCES

features & benefits

- Top, Bottom, or back feed.
- Units are shipped without holes for conduit.
- Spot drills for locating hole saw or knockouts are provided for top, bottom, or back feed.
- End user decides at installation whether top, bottom, or back feed is appropriate.
- No closure plug kits required.
- Units are not provided with conduit hubs.

Top 5 Resources

- Commercial & Industrial Products (Brochure)
- Disconnect Switch 30,60,100 Amp Outdoor/Indoor (Instruction Sheet No.)

specifications

General Info

- Type: Non-Fusible Safety Switch

Listing Agencies/Third Party Information

- CSA Listing Info: No
- CUL Listing No: No
- cU Lus: Yes
- cU Rus: No
- Federal Spec: No
- UL Listing No: No
- U N SPS C: 39121403
- U R: No

Technical Information


- Amps: 30 Amp
- Category Rating: Non-Fusible Safety Switches
- Volts: 600VAC
- Volts A C: 600

Buy American Act Compliance


- Country of Origin: UNITED STATES OF AMERICA
- Buy American Act Status: Buy American Act Compliant



resources
BROCHURE

 [Commercial & Industrial ProductsPDF \(3.52mb\)](#)

INSTRUCTION SHEET NO.

 [Disconnect Switch 30,60,100 Amp Outdoor/indoorPDF \(161.97kb\)](#)