

LWF2L2NhYmxlLXRyYXktd2lyZS1tZXNoLmFzcHhkFgJmDxYCHwAFggE8aW1nIHJlcGxhY2U9ImRzcmMilGRzcmM9Ii9+L21lZGIhLzAzNkQ4Qjk0OTREODQ:




designed to be better.

 Search

Pin & Sleeve Watertight Connector

PS4100C5W

Three pole, Four wire, Pin and Sleeve Connector. 100 amp, 3Ø/600 amp.



Representative image shown.

- SPECIFICATIONS
- RESOURCES

features & benefits

- All P&S Watertight Pin & Sleeve plugs, connectors, receptacles, and inlets bring you the features to enhance versatility, reliability, and safety.
- North American products come completely ready to wire, for quick, simple installation.
- And all feature chemical-resistant thermoplastic construction.
- Shrouded, nickel-plated, solid-brass pins provide corrosion protection and excellent conductivity.
- An exclusive, hinged cord grip eliminates loose parts that get lost.

Top 5 Resources

- Commercial & Industrial Products (Brochure)
- Pin & Sleeve (Installation Instructions)

specifications

General Info

- Type: Pin & Sleeve North American Watertight Connector
- Number Of Poles: 3
- Number Of Wires: 4

Listing Agencies/Third Party Information

- CSA Listing Info: No
- CUL Listing No: No
- cU Lus: Yes
- cU Rus: No
- Federal Spec: No
- UL Listing No: No
- U N SPS C: 39121403
- U R: No

Dimensions

- Length: 14.3"

Technical Information


- Amps: 100 Amp
- Volts: 3Ø 600VAC
- Volts A C: 600

Buy American Act Compliance


- Country of Origin: UNITED STATES OF AMERICA
- Buy American Act Status: Buy American Act Compliant



**resources
BROCHURE**

 [Commercial & Industrial ProductsPDF \(3.52mb\)](#)

INSTALLATION INSTRUCTIONS

 [Pin & SleevePDF \(1.43mb\)](#)