

XY+IDwvbGk+IDxsaSBjbGFzc0iY29sMil+IDxhIGlkPSJjdGwwNV9NYWluTmF2MV9jdGwwMI9ycHRDb21tZXJjaWFsX2N0bDAyX3JwdENvbW1lcmNpYWxTd



designed to be better.

Search

Fusible Mechanical Interlock

PS460FMIR7W

Triple pole, Four wire, Fusible Mechanical Interlock Receptacle. 6Ø amp, 480 vac.

Submit Query

Where to buy Enter Postal Code 0

[Email](#) [Print](#)



Representative image shown.

- SPECIFICATIONS
- RESOURCES

features & benefits

- Top or Bottom feed.
- Unit shipped with no holes drilled; a top and bottom feed spot drill is provided for locating hole saw or knockout.
- End user decides at installation whether top or bottom feed is appropriate.
- No closure plug kits required.

Top 5 Resources

- Commercial & Industrial Products (Brochure)
- Pin & Sleeve Fused Mechanical Interlock IEC 309-1, 309-2 Configuration 20, 30, 60, 100 amp Outdoor/indoor (Instruction Sheet No.)

specifications

General Info

- Type: Pin & Sleeve Fusible Mechanical Interlock
- Number Of Poles: 3
- Number Of Wires: 4

Listing Agencies/Third Party Information

- CSA Listing Info: No
- CUL Listing No: No
- cU Lus: Yes
- cU Rus: No
- Federal Spec: No
- UL Listing No: No
- U N SPS C: 39121403
- U R: No

Dimensions

- Depth (U S): 25.1
- Volume: 2201.019
- Weight: 12
- Width U S: 7.9
- Height: 11.1

Technical Information

- Amps: 60 Amp
- Volts: 3Ø 480VAC
- Volts A C: 480

Buy American Act Compliance


- Country of Origin: UNITED STATES OF AMERICA
- Buy American Act Status: Buy American Act Compliant



resources
BROCHURE

 [Commercial & Industrial ProductsPDF \(3.52mb\)](#)

INSTRUCTION SHEET NO.

 [Pin & Sleeve Fused Mechanical Interlock IEC 309-1, 309-2 Configuration 20, 30, 60, 100 amp Outdoor/indoorPDF \(10.66mb\)](#)