

XJzPC9hPiA8ZGI2IGNsYXNzPSJmb3VydGgtbHZsIGNvbDMiPiA8YSBpZD0iY3RsMDVFTWFpbk5hdjFfY3RsMDFfcnB0UmVzaWRlbnRpYWxfY3RsMTRfcnB0



designed to be better.

Search

Pin & Sleeve Watertight Plug

PS460P12W

Triple pole, Four wire, Pin and Sleeve Plug. 60 amp, 120/240 vac.

Submit Query

Where to buy 0

Email Print



Representative image shown.

- SPECIFICATIONS
- RESOURCES

features & benefits

- All P&S Watertight Pin & Sleeve plugs, connectors, receptacles, and inlets bring you the features to enhance versatility, reliability, and safety.
- North American products come completely ready to wire, for quick, simple installation.
- And all feature chemical-resistant thermoplastic construction.
- Shrouded, nickel-plated, solid-brass pins provide corrosion protection and excellent conductivity.
- An exclusive, hinged cord grip eliminates loose parts that get lost.

Top 5 Resources

- Commercial & Industrial Products (Brochure)
- Pin & Sleeve (Installation Instructions)

specifications

General Info

- Type: Pin & Sleeve North American Watertight Plug
- Number Of Poles: 3
- Number Of Wires: 4

Listing Agencies/Third Party Information

- CSA Listing Info: No
- CUL Listing No: No
- cU Lus: Yes
- cU Rus: No
- Federal Spec: No
- UL Listing No: No
- U N SPS C: 39121403
- U R: No

Dimensions

- Length: 10"

Technical Information


- Amps: 60 Amp
- Volts: 125/250VAC
- Volts A C: 125/250

Buy American Act Compliance


- Country of Origin: UNITED STATES OF AMERICA
- Buy American Act Status: Buy American Act Compliant



**resources
BROCHURE**

 [Commercial & Industrial ProductsPDF \(3.52mb\)](#)

INSTALLATION INSTRUCTIONS

 [Pin & SleevePDF \(1.43mb\)](#)