



designed to be better.

[Search](#)

Extra-Hard Use (EHU) Angle Plug, Black & Clear

PS5266HGAN

Straight Blade Plug 2pole 3wire 15amp 125v

[Submit Query](#)

Where to buy

[Submit Query](#)

0

[Email](#) [Print](#)



Representative image shown.

- [SPECIFICATIONS](#)
- [RESOURCES](#)

features & benefits

- Angle plugs and adapters both allow for 4-position face rotation.
- Tri-drive assembly and cord-grip screws are standard on all angle adapters.
- Angle adapter (sold separately as catalog number EHU15AN) will accommodate all Pass & Seymour EHU-style Straight Blade plugs and connectors on a retrofit basis. Simply remove the straight handle body from the plug or connector face assembly, and replace with the angle adapter.

Top 5 Resources

- [Commercial & Industrial Products \(Brochure\)](#)
- [Plugs & Connectors \(Brochure\)](#)

 Angle Plug or Connector, Cord diameter .300 to .690 (Installation Instructions)

specifications

General Info

- Color: Black
- Type: Angle devices

Listing Agencies/Third Party Information

- CSA Listing Info: C22.2 No.42
- CSA Standard: Yes
- CUL Listing No: No
- cU Lus: No
- cU Rus: No
- Federal Spec: Yes
- Fed Spec Number: WC596
- UL Listing No: 498
- UL Standard: Yes
- U N SPS C: 39121402
- U R: No

Dimensions

- Depth (U S): 1.35"
- Height U S: 2.13"
- Width U S: 1.53"

Technical Information



- Volts A C: 125

Buy American Act Compliance


- Country of Origin: MEXICO
- Buy American Act Status: Trade Agreement Act Compliant
-



resources BROCHURE

-  Commercial & Industrial ProductsPDF (3.52mb)
-  Plugs & ConnectorsPDF (1.93mb)

INSTALLATION INSTRUCTIONS

-  Angle Plug or Connector, Cord diameter .300 to .690PDF (103.33kb)