



designed to be better.

Heavy-Duty Spec Grade Receptacles, Back & Side Wire, 20A, 125V, Blue

PS5362BL

Heavy-Duty Spec Grade Duplex Receptacle Back & Side Wire 20amp 125volt Blue

Where to buy

0



Representative image shown.

AVAILABLE OPTIONS



Heavy-Duty Spec Grade Receptacles, Back & Side Wire, 20A, 125V, White



Heavy-Duty Spec Grade Receptacles, Back & Side Wire, 20A, 125V, Brown



Heavy-Duty Spec Grade Receptacles, Back & Side Wire, 20A, 125V, Black



Heavy-Duty Spec Grade Receptacles, Back & Side Wire, 20A, 125V, Gray



Heavy-Duty Spec Grade Receptacles, Back & Side Wire, 20A, 125V, Ivory



Heavy-Duty Spec Grade Receptacles, Back & Side Wire, 20A, 125V, Light Almond





Heavy-Duty Spec Grade Receptacles, Back & Side Wire, 20A, 125V, Red

- SPECIFICATIONS
- YOU MIGHT LIKE

features & benefits

- Heavy-duty, brass strap for added strength and ground conductivity.
- .032 inch thick, brass, triple-wipe power contacts for lasting retention.
- Strap tabs wrap around face to prevent strap from separating from face and back body.
- Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring.
- High strength nylon face.
- Internal screw-pressure-plate back and side wired to accept #14 and #10 AWG stranded or solid copper or copper-clad conductors.
- Eight back wire holes.
- Auto-ground clip assures positive ground.

specifications

General Info

- Color: blue
- Type: Receptacles
- Duty: Heavy Duty
- Special Features: Back, Side Wire

Listing Agencies/Third Party Information

- CSA Listing Info: C22.2 No. 42
- CSA Standard: Yes
- Federal Spec: Yes
- Fed Spec Number: WC596
- UL Listing No: UL498
- UL Standard: Yes
- U N SPS C: 39121406
- U R: No

Dimensions

- Depth (U S): 0.780"
- Height U S: 3.281"
- Width U S: 1.322"

Technical Information

- Amps: 20 Amp
- Volts: 125V
- Volts A C: 125
- Capacity: Duplex
- Grade Type: Specification

Buy American Act Compliance

- Country of Origin: MEXICO
- Buy American Act Status: Trade Agreement Act Compliant
-



you might like



Convention Center Floor Boxes

CCFB

[View Details](#)



880W Series Floor Boxes

880W

[View Details](#)



861 Series Raised Floor Boxes

861

[View Details](#)