

SJ2aWV3LW1vcmlUIGhyZWY9Ii93YWxsLXBsYXRlcy9hZG9ybmUuYXNweCl+VmldyBhZG9ybmUgV2FsbCBQbGF0ZXM8L2E+IDwvZGI2PiA8L2xpPiA8bGk



designed to be better.

Search

Extra-Hard Use (EHU) Specification Grade Plug, Black & White

PS5366X

Straight Blade Plug 2pole 3wire 20amp 125v

Submit Query

Where to buy Enter Postal Code

Submit Query

0

Email Print



Representative image shown.

- SPECIFICATIONS
- RESOURCES

features & benefits

- Unit arrives completely ready-to-wire, cuts installation time significantly.
- Nylon housing provides impact and chemical resistance.
- Rugged two-piece cord grip provides more uniform cord retention.
- Internal dust shield keeps terminals free of contaminants.
- Tri-drive assembly screws are standard on all Specification Grade plugs and connectors.
- All 3-wire terminals located on the same plane, allows for quick wire termination from any angle.
- Heavy-duty brass alloy blades and contacts, resist heat rise, provide excellent conductivity.
- Cord-grip screws recessed to protect installer against screwdriver head slippage.

Top 5 Resources

- Commercial & Industrial Products (Brochure)
- Plugs & Connectors (Brochure)
- Straight Blade EHU Plugs & Connectors, SF501R2 (Cutsheet)

specifications

General Info

- Color: White, Black

Listing Agencies/Third Party Information

- CSA Listing Info: No
- CUL Listing No: No
- cU Lus: Yes
- cU Rus: No
- Federal Spec: Yes
- UL Listing No: No
- U N SPS C: 39121402
- U R: No

Dimensions

- Depth (U S): 1.752"
- Height U S: 1.516"
- Width U S: 1.516"

Technical Information



- Volts A C: 125
- Grade Type: Specification

Buy American Act Compliance

- Country of Origin: MEXICO
- Buy American Act Status: Trade Agreement Act Compliant



resources
BROCHURE

-  [Commercial & Industrial ProductsPDF \(3.52mb\)](#)
-  [Plugs & ConnectorsPDF \(1.93mb\)](#)

CUTSHEET

-  [Straight Blade EHU Plugs & Connectors, SF501R2PDF \(179.75kb\)](#)