



designed to be better.

[Search](#)

Pin & Sleeve Watertight Plug

PS560P9W

Four pole, Five wire, Pin and Sleeve Plug. 6Ø amp, 120/208 vac.


[Submit Query](#)

Where to buy

[Submit Query](#)

0

[Email](#) [Print](#)



Representative image shown.

- [SPECIFICATIONS](#)
- [RESOURCES](#)

features & benefits

- All P&S Watertight Pin & Sleeve plugs, connectors, receptacles, and inlets bring you the features to enhance versatility, reliability, and safety.
- North American products come completely ready to wire, for quick, simple installation.
- And all feature chemical-resistant thermoplastic construction.
- Shrouded, nickel-plated, solid-brass pins provide corrosion protection and excellent conductivity.
- An exclusive, hinged cord grip eliminates loose parts that get lost.

Top 5 Resources

- [Commercial & Industrial Products \(Brochure\)](#)
- [Pin & Sleeve \(Installation Instructions\)](#)

specifications

General Info

- Type: Pin & Sleeve North American Watertight Plug
- Number Of Poles: 4
- Number Of Wires: 5

Listing Agencies/Third Party Information

- CSA Listing Info: No
- CUL Listing No: No
- cU Lus: Yes
- cU Rus: No
- Federal Spec: No
- UL Listing No: No
- U N SPS C: 39121403
- U R: No

Dimensions

- Length: 10"

Technical Information

- Amps: 60 Amp
- Volts: 3øY 120/208VAC
- Volts A C: 120/280

Buy American Act Compliance


- Country of Origin: UNITED STATES OF AMERICA
- Buy American Act Status: Buy American Act Compliant



resources BROCHURE

 Commercial & Industrial ProductsPDF (3.52mb)

INSTALLATION INSTRUCTIONS

 Pin & SleevePDF (1.43mb)