



designed to be better.

# Extra-Hard Use (EHU) Specification Grade Plug, Black & White

PS5666X

Straight Blade Plug 2pole 3wire 15amp 250v

Where to buy

0






Representative image shown.

- [SPECIFICATIONS](#)
- [RESOURCES](#)

## features & benefits

- Unit arrives completely ready-to-wire, cuts installation time significantly.
- Nylon housing provides impact and chemical resistance.
- Rugged two-piece cord grip provides more uniform cord retention.
- Internal dust shield keeps terminals free of contaminants.
- Tri-drive assembly screws are standard on all Specification Grade plugs and connectors.
- All 3-wire terminals located on the same plane, allows for quick wire termination from any angle.
- Heavy-duty brass alloy blades and contacts, resist heat rise, provide excellent conductivity.
- Cord-grip screws recessed to protect installer against screwdriver head slippage.

## Top 5 Resources

-  Commercial & Industrial Products (Brochure)
-  Plugs & Connectors (Brochure)
-  Straight Blade EHU Plugs & Connectors, SF501R2 (Cutsheet)

## specifications

### General Info

- Color: White, Black

### Listing Agencies/Third Party Information

- CSA Listing Info: No
- CUL Listing No: No
- cU Lus: Yes
- cU Rus: No
- Federal Spec: Yes
- UL Listing No: No
- U N SPS C: 39121402
- U R: No

### Dimensions

- Depth (U S): 1.752"
- Height U S: 1.516"
- Width U S: 1.516"

### Technical Information

- Volts A C: 250
- Grade Type: Specification



### Buy American Act Compliance

- Country of Origin: MEXICO
- Buy American Act Status: Trade Agreement Act Compliant
- 



## resources

### BROCHURE

-  Commercial & Industrial ProductsPDF (3.52mb)
-  Plugs & ConnectorsPDF (1.93mb)

### CUTSHEET

-  Straight Blade EHU Plugs & Connectors, SF501R2PDF (179.75kb)