

WNIPJSJkc3JjIiBkc3JjPSlvi9tZWRpYS8wNDZDNzI3QjA5Njg0QkJKGODAyMEU1NjM2MjNBMjZBQS5hc2h4IiBhbHQ9ImZpYmVylGNhc3NldHRlcylgd2lkdGg9JjI



designed to be better.

Search

MaxGrip M3 Plug, Yellow

PS5965Y

Straight Blade Plug 2pole 3wire 15amp 125v

Submit Query

Where to buy

Submit Query

0



Representative image shown.

- SPECIFICATIONS
- RESOURCES

features & benefits

- Tough nylon construction with crush / impact resistance that exceeds hospital grade and Fed Spec requirements; arc resistance exceeds UL requirements.
- Self-hinge swings wide open to make quick, easy work of light, clean connections. Insert conductors into terminals and tighten terminal screws; close hinge housing around cord and tighten housing screws.
- Enclosed terminals provide solid, internally-clamped connections.
- Molded finger grips promote safe, sure handling.
- High-visibility yellow and orange, or gray.
- Hospital Grade version displays the Hospital Grade green dot.

Top 5 Resources

- Plugs & Connectors (Brochure)
- Straight Blade Heavy Duty MaxGrip M3 Plugs & Connectors, SF502R2 (Cutsheet)

specifications

General Info

- Color: Yellow
- Product Series: MaxGrip
- Type: Plug

Listing Agencies/Third Party Information

- CSA Listing Info: Yes
- cU Lus: Yes
- cU Rus: No
- Federal Spec: No
- UL Listing No: Yes
- U N SPS C: 39121402
- U R: No

Dimensions

- Height U S: 1.83"
- Width U S: 1.34"

Technical Information

- Amps: 15 Amp
- Volts: 125V
- Volts A C: 125

Buy American Act Compliance


- Country of Origin: MEXICO
- Buy American Act Status: Trade Agreement Act Compliant



resources
BROCHURE

 [Plugs & ConnectorsPDF \(1.93mb\)](#)

CUTSHEET

 [Straight Blade Heavy Duty MaxGrip M3 Plugs & Connectors, SF502R2PDF \(182.91kb\)](#)