

vL2F1ZGlvLWtpdHMvc3R1ZGlvLWRlc2lnbi9hdTU3MTIttd2guYXNweGQWAmYPFglfAAU8bHlyaVEgQ2hhcmdllCYgUGxheSBUd28tWm9uZSBLaXQgaW4gU3



designed to be better.

 Search

## Non-Fusible Safety Switch

PS60SS

Non-Fusible Safety Switch. 60 amp, 600 vac.







Representative image shown.

- SPECIFICATIONS
- RESOURCES

### features & benefits

- Top, Bottom, or back feed.
- Units are shipped without holes for conduit.
- Spot drills for locating hole saw or knockouts are provided for top, bottom, or back feed.
- End user decides at installation whether top, bottom, or back feed is appropriate.
- No closure plug kits required.
- Units are not provided with conduit hubs.

### Top 5 Resources

- Commercial & Industrial Products (Brochure)
- Disconnect Switch 30,60,100 Amp Outdoor/Indoor (Instruction Sheet No.)

### specifications

#### General Info

- Type: Non-Fusible Safety Switch

#### Listing Agencies/Third Party Information

- CSA Listing Info: No
- CUL Listing No: No
- cU Lus: Yes
- cU Rus: No
- Federal Spec: No
- UL Listing No: No
- U N SPS C: 39121403
- U R: No

#### Technical Information


- Amps: 60 Amp
- Category Rating: Non-Fusible Safety Switches
- Volts: 600VAC
- Volts A C: 600

#### Buy American Act Compliance


- Country of Origin: UNITED STATES OF AMERICA
- Buy American Act Status: Buy American Act Compliant



**RESOURCES**  
**BROCHURE**

 [Commercial & Industrial ProductsPDF \(3.52mb\)](#)

**INSTRUCTION SHEET NO.**

 [Disconnect Switch 30,60,100 Amp Outdoor/indoorPDF \(161.97kb\)](#)