

D0iMjE4liBoZWlnaHQ9IjExMiiLgZ5kAgUPDXyCHwQFNy9lbGVjdHJpY2FsLXdpclluZy1kZXZpY2VzL2ZsZXhjb3ItZS1iZXNoLWdyaXBzLmFzCHhkFgICAC



designed to be better.

Search

## Series 15 In-Line Connectors

PSM2MBK

150A 600V MALE CAM TYPE PLUG BLK

Submit Query

Where to buy

Submit Query

0

Email Print



Representative image shown.

- SPECIFICATIONS
- RESOURCES

### features & benefits

Thermoplastic elastomer housing for outstanding impact and chemical resistance, as well as an exceptional seal for maintaining NEMA Type 3R and 4 integrity. Non-conductive retaining screw helps to insure no contact with live parts, along with providing stability to the fully assembled product. Heavy-duty brass male and female contacts provide a superior and consistent means of conductivity. Heavy-duty hex set screws allow greater termination torque. Copper wire provides quality strain relief. Copper shim bundles wire strands to reduce "splaying."

### Top 5 Resources

- [Cam-Type Devices \(Brochure\)](#)
- [Commercial & Industrial Products \(Brochure\)](#)
- [Plugs & Connectors \(Brochure\)](#)

### specifications

#### General Info

- Color: Black
- Type: In line connectors male

#### Listing Agencies/Third Party Information

- CSA Listing Info: cCSAus
- CSA Standard: Yes
- UL Listing No: UL
- UL Standard: Yes
- U N SPS C: 39121403

#### Dimensions

- Length: 4.30"

#### Buy American Act Compliance

- Country of Origin: MEXICO
- Buy American Act Status: Trade Agreement Act Compliant



### resources

#### BROCHURE

- [Cam-Type DevicesPDF \(1.27mb\)](#)
- [Commercial & Industrial ProductsPDF \(3.52mb\)](#)
- [Plugs & ConnectorsPDF \(1.93mb\)](#)