

glBDxYCHwAFDkR1cGxleCBPdXRrsZXRzZAIED2QWBgJBDw8WAh8EBR4vZWxIY3RyaWNhbC1vdXRrsZXRzL2dmY2lzMmFzcHhkFgJmDxYCHwAFDEdGQ0l



designed to be better.

Search

# PlugTail™ Specification Grade GFCI Receptacle, White

PT2095W

PlugTail GFCI Receptacle, 10kA SCCR, 20A 125VAC, White

Submit Query

Where to buy

Submit Query

Like 0 Tweet 0

0 Email Print





- 

### product gallery

Representative images shown.

### AVAILABLE OPTIONS

PlugTail™ Specification Grade GFCI Receptacle, Brown

PlugTail™ Specification Grade GFCI Receptacle, Black

PlugTail™ Specification Grade GFCI Receptacle, Gray

PlugTail™ Specification Grade GFCI Receptacle, Ivory

PlugTail™ Specification Grade GFCI Receptacle, Light Almond

PlugTail™ Specification Grade GFCI Receptacle, Red






- SPECIFICATIONS

- RESOURCES

## features & benefits

- Faster, more reliable installation.
- No exposed terminals create a finger safe application before, during, and after installation.
- Built-in connector features large brass terminal blades to ensure consistent, reliable electrical connections to PlugTail Connector.
- GFCI works with the existing 3 wire PlugTail Connectors creating a non-feed-thru application for facility owners. At rough-in just install the same right angle connector for GFCI and receptacle openings.
- SafeLock™ Protection: if critical components are damaged and ground fault protection is lost, power to receptacle is disconnected.
- FSUL Listed (Federal Specification WC596).
- Exceeds UL943 voltage surge requirements; survives 100x the required UL 3kA/6kV voltage surge test cycles.
- Trip indicator light (red LED).
- Mounting screws are shipped captive in the device and wall plate for easier installation.
- High-impact-resistant thermoplastic construction.
- Zinc-plated steel mounting strap.
- Button colors match the device face.
- Dual-direction test and reset buttons.
- Class A rated GFCI.
- Supplied with matching TP26 nylon wall plate.
- Tri-drive screws.

## Top 5 Resources

-  [PlugTail Wiring Devices \(Brochure\)](#)
-  [GFCI Test & Protect \(Brochure\)](#)
-  [PlugTail Spec Grade GFCIs, SF1104R2 \(Cutsheet\)](#)
-  [Commercial & Industrial Products \(Brochure\)](#)
-  [PlugTail GFCI Receptacle \(Installation Instructions\)](#)

## specifications

### General Info

- Color: White
- Product Series: PlugTail
- Type: GFCI Receptacle
- Style: Decorator

### Listing Agencies/Third Party Information

- CSA Listing Info: C22.2 No. 42 & 144
- CSA Standard: Yes
- cULus: Yes
- Federal Spec: Yes
- Fed Spec Number: WC596
- UL Listing No: UL943, UL498
- UL Standard: Yes
- U N SPS C: 39121614

### Dimensions

- Depth (U S): 1.2"
- Height U S: 4.2"
- Width U S: 1.72"

### Technical Information




- Amps: 20 Amp
- Volts: 125
- Volts A C: 120
- Grade Type: Specification

### Buy American Act Compliance

- Country of Origin: CHINA
- Buy American Act Status: No
- 

## resources



### BROCHURE

-  [PlugTail Wiring DevicesPDF \(1.39mb\)](#)
-  [GFCI Test & ProtectPDF \(494.1kb\)](#)
-  [Commercial & Industrial ProductsPDF \(3.52mb\)](#)

### CUTSHEET

-  [PlugTail Spec Grade GFCIs, SF1104R2PDF \(420.45kb\)](#)

### INSTALLATION INSTRUCTIONS

-  [PlugTail GFCI ReceptaclePDF \(204.75kb\)](#)
-  [Installation et test d'une prise DDFT PlugTail™PDF \(382.66kb\)](#)