

xhY2U9ImRzcmMiiGRzcmM9li9+L21IZGihLzdEODg1ODc0MzI3NDQzMEY5MjM5OUZDMTkyMDM1RkM0LmFzaHgilGFsdD0iUG93ZXIlgRGlzdHJpYnV0aW9t



designed to be better.

Search

PlugTail™ Single Pole 20 amp Toggle Switch, White

PT20AC1W

PlugTail™ Single Pole Toggle Switch, 20amp 120/277vac, White

Also available in Ivory (PT20AC1I), Light Almond (PT20AC1LA), Gray (PT20AC1GRY), Red (PT20AC1RED) and Brown (PT20AC1).

Submit Query

Where to buy

Submit Query

Like 0 Tweet 0

0
Email Print





•

•

product gallery

Representative images shown.

AVAILABLE OPTIONS

PlugTail™ Single Pole 20 amp Toggle Switch, Brown

PlugTail™ Single Pole 20 amp Toggle Switch, Gray

PlugTail™ Single Pole 20 amp Toggle Switch, Ivory

PlugTail™ Single Pole 20 amp Toggle Switch, Light Almond

PlugTail™ Single Pole 20 amp Toggle Switch, Red

- SPECIFICATIONS
- RESOURCES

features & benefits

- Ground wire pre-mounted to the box
- Mud ring factory installed
- 4" square x 1 1/2" or 2 1/8" metal boxes
- PlugTail Right Angle Connectors with 12 AWG copper pigtails
- All Double Gang Kits contain two right angle PlugTail connectors

Top 5 Resources

-  [PlugTail Switches, SF1510R1 \(Cutsheet\)](#)
-  [PlugTail Wiring Devices \(Brochure\)](#)
-  [Commercial & Industrial Products \(Brochure\)](#)

specifications

General Info

- Color: White

- Product Series: PlugTail
- Type: Toggle
- Number Of Poles: 1

Listing Agencies/Third Party Information

- CSA Listing Info: C22.2 111
- CSA Standard: Yes
- cU Lus: Yes
- Federal Spec: Yes
- Fed Spec Number: WS896
- U N SPS C: 39121507

Dimensions

- Depth (U S): 1.073"
- Height U S: 3.281"
- Width U S: 1.320"

Technical Information

- Amps: 20 Amp
- Volts: 120/277VAC
- Volts A C: 120/277
- Grade Type: Industrial


Buy American Act Compliance

- Country of Origin: MEXICO
- Buy American Act Status: Trade Agreement Act Compliant
-

resources BROCHURE

-  PlugTail Wiring DevicesPDF (1.39mb)
-  Commercial & Industrial ProductsPDF (3.52mb)

CUTSHEET

-  PlugTail Switches, SF1510R1PDF (364.61kb)