

Y9li93aXJILWNhYmxllW1hbmFnZW1lbnQuYXNweCI+V2lyZSAmIENhYmxllE1hbmFnZW1lbnQ8L2E+IDx1bCBjbGFz0iaGlkZS1uZXciPiA8bGkgY2xhc3M9li



designed to be better.

Search

PlugTail™ Decorator Spec Grade Receptacles, 20A, 125V, White

PT26352W

PlugTail™ Decorator Spec Grade Duplex Receptacle 20amp 125volt White

Submit Query

Where to buy

Submit Query

Like 0 Tweet 0 0 Email Print





product gallery

Representative images shown.

AVAILABLE OPTIONS

PlugTail™ Decorator Spec Grade Receptacles, 20A, 125V, Brown

PlugTail™ Decorator Spec Grade Receptacles, 20A, 125V, Black

PlugTail™ Decorator Spec Grade Receptacles, 20A, 125V, Gray

PlugTail™ Decorator Spec Grade Receptacles, 20A, 125V, Ivory

PlugTail™ Decorator Spec Grade Receptacles, 20A, 125V, Light Almond

PlugTail™ Decorator Spec Grade Receptacles, 20A, 125V, Red

- SPECIFICATIONS
- YOU MIGHT LIKE
- RESOURCES

features & benefits

- .036 inch thick, brass, triple-wipe power contacts for lasting retention.
- Plated steel wrap strap design for maximum durability and corrosion resistance.
- No exposed terminals create a finger safe application before, during, and after installation.
- Built-in connector features large brass terminal blades to ensure consistent, reliable electrical connections.

- Crimped and welded contacts.
- Ultrasonically welded polycarbonate connector housing secures terminations and conductors in a UL Listed, finger safe housing.
- Large brass contacts snugly terminate on device blade terminals.
- Pre-stripped connector leads fasten to conductors, easier than standard pigtails.
- Auto-ground clip assures positive ground.

Top 5 Resources

-  [PlugTail Wiring Devices \(Brochure\)](#)
-  [GFCI Receptacles \(Brochure\)](#)
-  [Commercial & Industrial Products \(Brochure\)](#)

specifications

General Info

- Color: white
- Product Series: PlugTail
- Type: Receptacles
- Number Of Poles: 2
- Number Of Wires: 3
- Style: Decorator

Listing Agencies/Third Party Information

- cU Lus: Yes
- Federal Spec: Yes
- Fed Spec Number: WC596
- UL Listing No: UL498
- UL Standard: Yes
- U N SPS C: 39121406

Dimensions

- Depth (U S): 0.625"
- Height U S: 3.281"
- Width U S: 1.5"

Technical Information

- Amps: 20 Amp
- Volts: 125V
- Volts A C: 125
- Capacity: Duplex
- Grade Type: Federal Specification

Buy American Act Compliance

- Country of Origin: MEXICO
- Buy American Act Status: Trade Agreement Act Compliant
-

you might like

500/700 Series Small Raceway

500/700

[View Details](#)




4000 Large Steel Prewired Raceway

4000-PW

[View Details](#)

resources

BROCHURE

-  [PlugTail Wiring DevicesPDF \(1.39mb\)](#)
-  [GFCI ReceptaclesPDF \(1.19mb\)](#)
-  [Commercial & Industrial ProductsPDF \(3.52mb\)](#)