

YXRlcyld2lkdGg9ljlxOCIGA0VpZ2h0PSIxMTIiIC8+ZAI0FDw8WAh8EBRgvd2FsbC1wbGF0ZXMvZHVwbGV4LmFzcHhkFgICAQ8WAh8ABRJEEdXBsZXggV2Fs



designed to be better.

Search

# PlugTail™ Industrial Extra Heavy-Duty Spec Grade Receptacles, 20A, 125V, White

PT5362AW  
PlugTail™ Industrial Extra Heavy-Duty Spec Grade Duplex Receptacle 20amp 125volt White


Submit Query

Where to buy Enter Postal Code

Submit Query

Like 0 Tweet 0

0 Email Print





**product gallery**  
Representative images shown.  
**AVAILABLE OPTIONS**

PlugTail™ Industrial Extra Heavy-Duty Spec Grade Receptacles, 20A, 125V, Brown

PlugTail™ Industrial Extra Heavy-Duty Spec Grade Receptacles, 20A, 125V, Black

PlugTail™ Industrial Extra Heavy-Duty Spec Grade Receptacles, 20A, 125V, Blue

PlugTail™ Industrial Extra Heavy-Duty Spec Grade Receptacles, 20A, 125V, Gray

PlugTail™ Industrial Extra Heavy-Duty Spec Grade Receptacles, 20A, 125V, Ivory

PlugTail™ Industrial Extra Heavy-Duty Spec Grade Receptacles, 20A, 125V, Light Almond




PlugTail™ Industrial Extra Heavy-Duty Spec Grade Receptacles, 20A, 125V, Red

- SPECIFICATIONS
- RESOURCES

## features & benefits

- .036 inch thick, brass, triple-wipe power contacts for lasting retention.
- No exposed terminals create a finger safe application before, during, and after installation.
- Built-in connector features large brass terminal blades to ensure consistent, reliable electrical connections.
- Crimped and welded contacts.
- Ultrasonically welded polycarbonate connector housing secures terminations and conductors in a UL Listed, finger safe housing.
- Large brass contacts snugly terminate on device blade terminals.
- Pre-stripped connector leads fasten to conductors, easier than standard pigtails.
- Auto-ground clip assures positive ground.

## Top 5 Resources

-  [PlugTail Wiring Devices \(Brochure\)](#)
-  [GFCI Receptacles \(Brochure\)](#)
-  [Commercial & Industrial Products \(Brochure\)](#)

## specifications

### General Info

- Color: white
- Product Series: PlugTail
- Type: Receptacles
- Duty: Heavy Duty

### Listing Agencies/Third Party Information

- cU Lus: Yes
- Federal Spec: Yes
- Fed Spec Number: WC596
- UL Listing No: UL498
- UL Standard: Yes
- U N SPS C: 39121406
- U R: No

### Dimensions

- Depth (U S): .866"
- Height U S: 3.281"
- Width U S: 1.625"

### Technical Information




- Amps: 20 Amp
- Volts: 125V
- Volts A C: 125
- Capacity: Duplex
- Grade Type: Industrial

### Buy American Act Compliance

- Country of Origin: MEXICO
- Buy American Act Status: Trade Agreement Act Compliant
- 

## resources

### BROCHURE

-  [PlugTail Wiring DevicesPDF \(1.39mb\)](#)
-  [GFCI ReceptaclesPDF \(1.19mb\)](#)
-  [Commercial & Industrial ProductsPDF \(3.52mb\)](#)