

2N0bDayX3JwdENvbW1lcmNpYWxfY3RsMDJfcuB0Q29tbWVvY2lhbFN1Ym1lbnVfY3RsMDfaGxWaWV3TGluaylgY2xhc3M9InZpZXctbW9yZSIgaHJlZj0iL2V:



designed to be better.

Search

PlugTail™ Spec Grade Receptacles, 20A, 125V, Light Almond

PT5362LA

PlugTail™ Spec Grade Duplex Receptacle 20amp 125volt Light Almond

Submit Query

Where to buy

Submit Query

Like 0 Tweet 0

0

Email Print





product gallery
Representative images shown.
AVAILABLE OPTIONS

PlugTail™ Spec Grade Receptacles, 20A, 125V, White

PlugTail™ Spec Grade Receptacles, 20A, 125V, Brown

PlugTail™ Spec Grade Receptacles, 20A, 125V, Black

PlugTail™ Spec Grade Receptacles, 20A, 125V, Blue

PlugTail™ Spec Grade Receptacles, 20A, 125V, Gray

PlugTail™ Spec Grade Receptacles, 20A, 125V, Ivory





PlugTail™ Spec Grade Receptacles, 20A, 125V, Red

- SPECIFICATIONS
- RESOURCES

features & benefits

- .036 inch thick, brass, triple-wipe power contacts for lasting retention.
- Plated steel wrap strap design for maximum durability and corrosion resistance.
- No exposed terminals create a finger safe application before, during, and after installation.
- Built-in connector features large brass terminal blades to ensure consistent, reliable electrical connections.
- Ultrasonically welded polycarbonate connector housing secures terminations and conductors in a UL Listed, finger safe housing.
- Crimped and welded contacts.
- Large brass contacts snugly terminate on device blade terminals.
- Pre-stripped connector leads fasten to conductors, easier than standard pigtails.
- Auto-ground clip assures positive ground.

Top 5 Resources

-  [PlugTail Wiring Devices \(Brochure\)](#)
-  [GFCI Receptacles \(Brochure\)](#)
-  [Commercial & Industrial Products \(Brochure\)](#)
-  [PlugTail Specification Grade Receptacles, SF1505R2 \(Cutsheet\)](#)

specifications

General Info

- Color: white
- Product Series: PlugTail
- Type: Receptacles
- Special Features: split circuit

Listing Agencies/Third Party Information

- CUL Listing No: UL498
- cU Lus: Yes
- Federal Spec: Yes
- Fed Spec Number: WC596
- UL Listing No: UL498
- U N SPS C: 39121406
- U R: No

Dimensions

- Depth (U S): .625"
- Height U S: 3.281"
- Width U S: 1.5"

Technical Information




- Amps: 20 Amp
- Volts: 125V
- Volts A C: 125
- Capacity: Duplex
- Grade Type: Federal Specification

Buy American Act Compliance

- Country of Origin: MEXICO
- Buy American Act Status: Trade Agreement Act Compliant
-

resources

BROCHURE

-  [PlugTail Wiring DevicesPDF \(1.39mb\)](#)
-  [GFCI ReceptaclesPDF \(1.19mb\)](#)
-  [Commercial & Industrial ProductsPDF \(3.52mb\)](#)

CUTSHEET

-  [PlugTail Specification Grade Receptacles, SF1505R2PDF \(300.44kb\)](#)