



designed to be better.

PlugTail™ Extra Heavy-Duty Hospital Grade Receptacles, 20A, 125V, Ivory

PT8300I

PlugTail™ Extra Heavy-Duty Hospital Grade Duplex Receptacle 20amp 125volt Ivory

Where to buy

Like





product gallery

Representative images shown.

AVAILABLE OPTIONS

PlugTail™ Extra Heavy-Duty Hospital Grade Receptacles, 20A, 125V, White

PlugTail™ Extra Heavy-Duty Hospital Grade Receptacles, 20A, 125V, Brown

PlugTail™ Extra Heavy-Duty Hospital Grade Receptacles, 20A, 125V, Black

PlugTail™ Extra Heavy-Duty Hospital Grade Receptacles, 20A, 125V, Blue

PlugTail™ Extra Heavy-Duty Hospital Grade Receptacles, 20A, 125V, Gray

PlugTail™ Extra Heavy-Duty Hospital Grade Receptacles, 20A, 125V, Light Almond




PlugTail™ Extra Heavy-Duty Hospital Grade Receptacles, 20A, 125V, Red

- SPECIFICATIONS
- RESOURCES

features & benefits

- .036 inch thick, brass, triple-wipe power contacts for lasting retention.
- Plated steel wrap strap design for maximum durability and corrosion resistance.
- No exposed terminals create a finger safe application before, during, and after installation.
- Built-in connector features large brass terminal blades to ensure consistent, reliable electrical connections.
- Crimped and welded contacts.
- Ultrasonically welded polycarbonate connector housing secures terminations and conductors in a UL Listed, finger safe housing.
- Large brass contacts snugly terminate on device blade terminals.
- Pre-stripped connector leads fasten to conductors, easier than standard pigtails.
- Auto-ground clip assures positive ground.

Top 5 Resources

-  PlugTail Wiring Devices (Brochure)
-  Commercial & Industrial Products (Brochure)
-  PlugTail Hospital Grade Extra Heavy Duty Receptacles, SF716R2 (Cutsheet)

specifications

General Info

- Color: Ivory
- Product Series: PlugTail
- Type: Receptacles
- Duty: Extra Heavy Duty

Listing Agencies/Third Party Information

- cU Lus: Yes
- Federal Spec: Yes
- Fed Spec Number: WC596
- UL Listing No: UL498
- UL Standard: Yes
- U N SPS C: 39121406
- U R: No

Dimensions

- Depth (U S): .866"
- Height U S: 3.281"
- Width U S: 1.625"

Technical Information



- Amps: 20 Amp
- Volts: 125V
- Volts A C: 125
- Capacity: Duplex
- Grade Type: Hospital

Buy American Act Compliance

- Country of Origin: MEXICO
- Buy American Act Status: Trade Agreement Act Compliant
-

resources

BROCHURE

-  PlugTail Wiring DevicesPDF (1.39mb)
-  Commercial & Industrial ProductsPDF (3.52mb)

CUTSHEET

 PlugTail Hospital Grade Extra Heavy Duty Receptacles, SF716R2PDF (200.06kb)