

3NIIERldmjZXNkAgMPDxYCHwQFNC9IbGVjdHJpY2FsLWFjY2Vzc29yaWVzL3NwZWNPYWwtcHVycG9zZS1kZXZpY2VzLmFzcHhkFgJmDxYCHwAFgwE8a



designed to be better.

Search

# PlugTail™ Connectors, Right Angle, Solid, 6"

PTR6SOL

PlugTail™ Connectors Right Angle Solid 6"

Submit Query

Where to buy

Submit Query

Like 0 Tweet 0 0 Email Print





## product gallery

Representative images shown.

- SPECIFICATIONS
- RESOURCES

## features & benefits

- Ultrasonically welded polycarbonate connector housing secures terminations and conductors in a UL Listed, finger safe housing.
- Large brass contacts snugly terminate on device blade terminals.
- Pre-stripped connector leads fasten to conductors, easier than standard pigtailed.
- Available in any wire length up to 25 inches, use Configurable Solutions to order.

## Top 5 Resources

-  [PlugTail Wiring Devices \(Brochure\)](#)
-  [Commercial & Industrial Products \(Brochure\)](#)

## specifications

### General Info

- Product Series: PlugTail
- Type: connectors
- Special Features: Right angle, solid

### Listing Agencies/Third Party Information

- CSA Listing Info: No
- CUL Listing No: No
- cU Lus: Yes
- cU Rus: No
- Federal Spec: No
- UL Listing No: No
- U N SPS C: 39121406
- U R: No

### Dimensions

- Height U S: 6.375"

### Buy American Act Compliance

- Country of Origin: CHINA
- Buy American Act Status: No

## resources

### BROCHURE

-  [PlugTail Wiring DevicesPDF \(1.39mb\)](#)
-  [Commercial & Industrial ProductsPDF \(3.52mb\)](#)