

GltZyByZXBsYWNIPSJkc3JjliBkc3JjPSlvi9tZWRpYS8xQzQzODdDQUNGOI0MEYwOTUwMjE4REQ5RDY1MDdCRi5hc2h4IiBhbHQ9IiN1cmdlIFByb3RIY3R



designed to be better.

Search

PlugTail™ Connectors, Right Angle, Stranded, 6"

PTR6STR

PlugTail™ Connectors Right Angle Stranded 6"

Submit Query

Where to buy Enter Postal Code

Submit Query



Like 0

Tweet 0

0

Email Print





product gallery

Representative images shown.

- SPECIFICATIONS
- RESOURCES

features & benefits

- Ultrasonically welded polycarbonate connector housing secures terminations and conductors in a UL Listed, finger safe housing.
- Large brass contacts snugly terminate on device blade terminals.
- Pre-stripped connector leads fasten to conductors, easier than standard pigtailed.
- Available in any wire length up to 25 inches, use Configurable Solutions to order.

Top 5 Resources

-  PlugTail Wiring Devices (Brochure)
-  Commercial & Industrial Products (Brochure)

specifications

General Info

- Product Series: PlugTail
- Type: connectors
- Special Features: right angle, stranded

Listing Agencies/Third Party Information

- CSA Listing Info: No
- CUL Listing No: No
- cU Lus: Yes
- cU Rus: No
- Federal Spec: No
- UL Listing No: No
- U N SPS C: 39121406
- U R: No

Dimensions

- Height U S: 6.375"

Buy American Act Compliance

- Country of Origin: CHINA
- Buy American Act Status: No

resources

BROCHURE

-  PlugTail Wiring DevicesPDF (1.39mb)
-  Commercial & Industrial ProductsPDF (3.52mb)