

aWFsTGluaylgY2xhc3M9ImhpZGUtbnV3liBocmVmPSIvY29tbWVyY2lhbC1hdi5hc3B4lj5Db21tZXJjaWFsIEEevVjwvYT4gPHVsiGNsYXNzPSJoaWRILW5ldyl+



designed to be better.

Search

# P&S PlugTail™ Switch Right Angle Connector 3-Wire, 6" Stranded THHN12

PTS6STR3

P&S PlugTail™ Switch Right Angle Connector, 3-wire, 6" Stranded THHN12, Colors Green, Black, Black

Submit Query

Where to buy

Submit Query

Like 0 Tweet 0

0 Email Print





## product gallery



Representative images shown.

- SPECIFICATIONS
- RESOURCES

## features & benefits

- All PlugTail™ Connectors are available in any wire length up to 25 inches
- Large crimped and welded brass contacts
- Ultrasonically welded polycarbonate connector housing secures terminations and conductors in a UL Listed, finger safe housing. Audible snapping latch assures connection, allows release.
- Pre-stripped connector leads fasten to conductors, easier than standard pigtails.

## Top 5 Resources

-  [PlugTail Decorator Switches, SF1511R2 \(Cutsheet\)](#)
-  [PlugTail Switches, SF1510R1 \(Cutsheet\)](#)
-  [PlugTail Wiring Devices \(Brochure\)](#)

## specifications

### General Info

- Product Series: PlugTail
- Type: Right Angle Connector
- Number Of Poles: 1
- Number Of Wires: 3
- Style: Decorator

## Buy American Act Compliance



- Country of Origin: MEXICO
- Buy American Act Status: Trade Agreement Act Compliant

## resources

### BROCHURE

-  [PlugTail Wiring DevicesPDF \(1.39mb\)](#)

### CUTSHEET

-  [PlugTail Decorator Switches, SF1511R2PDF \(359.46kb\)](#)
-  [PlugTail Switches, SF1510R1PDF \(364.61kb\)](#)