



designed to be better.

# P&S PlugTail™ Switch Right Angle Connector 4-Wire, 6" Stranded THHN12

PTS6STR4

P&S PlugTail™ Switch Right Angle Connector, 4-wire, 6" Stranded THHN12, Colors Green, Red, Red, Black

Where to buy

Like



-



## product gallery




Representative images shown.

- SPECIFICATIONS
- RESOURCES

## features & benefits

- All PlugTail™ Connectors are available in any wire length up to 25 inches
- Large crimped and welded brass contacts
- Ultrasonically welded polycarbonate connector housing secures terminations and conductors in a UL Listed, finger safe housing. Audible snapping latch assures connection, allows release.
- Pre-stripped connector leads fasten to conductors, easier than standard pigtails.

## Top 5 Resources

-  [PlugTail Decorator Switches, SF1511R2 \(Cutsheet\)](#)
-  [PlugTail Switches, SF1510R1 \(Cutsheet\)](#)
-  [PlugTail Wiring Devices \(Brochure\)](#)

## specifications

### General Info

- Product Series: PlugTail
- Type: Right Angle Connector
- Number Of Poles: 3-way
- Number Of Wires: 4
- Style: Decorator

## Buy American Act Compliance


- Country of Origin: MEXICO
- Buy American Act Status: Trade Agreement Act Compliant
-


## **resources**

### **BROCHURE**

 [PlugTail Wiring DevicesPDF \(1.39mb\)](#)

### **CUTSHEET**

 [PlugTail Decorator Switches, SF1511R2PDF \(359.46kb\)](#)

 [PlugTail Switches, SF1510R1PDF \(364.61kb\)](#)