

4liBoZWInaHQ9ljExMilgLz5kAgUPDxYCHwQFNi9IbGVjdHJpY2FsLXdpcmluZy1kZXZpY2VzL2VsZWN0cmJjYWwtYWNjZXNzb3JpZXMuYXNweGQWAglBDxY



designed to be better.

Search

# Digital Timer, Ivory

RT1I  
7-BUTTON TIMER 120VAC 1/6 HP, IVORY

Submit Query

Where to buy

Submit Query

Like 0 Tweet 0

0  
Email Print



## product gallery

Representative images shown.

### AVAILABLE OPTIONS





Digital Timer, White



Digital Timer, Black



Digital Timer, Light Almond

- SPECIFICATIONS
- RESOURCES

## features & benefits

- Seven-button preset time switch.
- Manual ON/OFF.
- Adjustable time delay: 1, 5, 10, 20, 30, 60 minutes.
- Lighted switch for visibility in darkened rooms.
- Controls most types of lighting.
- cULus listed.
- 5-year warranty.
- Load: Incandescent, fluorescent, compact fluorescent (CFL), magnetic low-voltage (MLV) and electronic low-voltage (ELV), 1/6 hp.

## Top 5 Resources

- [Sensors & Timers \(Brochure\)](#)
- [Commercial Lighting Controls \(Brochure\)](#)
- [Time Switch 7 Button Preset, RT1 \(Installation Instructions\)](#)

## specifications

### General Info

- Color: Ivory
- Type: 7-Button Digital Timer

### Listing Agencies/Third Party Information

- cU Lus: Yes
- U N SPS C: 39121502

### Dimensions

- Depth (U S): 1.88"
- Height U S: 3.281"
- Width U S: 1.69"

### Technical Information

- Volts: 120VAC
- Volts A C: 120
- Watts: 0-600

### Buy American Act Compliance

- Country of Origin: CHINA
- Buy American Act Status: No
- 

## resources

### BROCHURE

- [Sensors & TimersPDF \(578.46kb\)](#)
- [Commercial Lighting ControlsPDF \(323.03kb\)](#)

### INSTALLATION INSTRUCTIONS

- [Time Switch 7 Button Preset, RT1PDF \(282.54kb\)](#)