



designed to be better.

Residential Occupancy Sensor, White




RWU600UWCC4

Single Pole Occupancy Sensor, 3-Wire 600W, White

Where to buy

Like



- 
- 
- 

product gallery

Representative images shown.

AVAILABLE OPTIONS



Residential Occupancy Sensor, Black



Residential Occupancy Sensor, Ivory







Residential Occupancy Sensor, Light Almond

- SPECIFICATIONS
- RESOURCES

features & benefits

- Replaces a standard light or fan single pole switch.
- Lighted switch for visibility in darkened rooms.
- Automatic-ON operation.
- Fixed five-minute time delay.
- Low-profile styling with uniform color-matched lens and device.
- Coverage: 180 degrees, max. 600 ft.2 (56m2)
- cULus listed.
- 5-year warranty.
- Works with most common residential lighting types.
- RWU600U only -- Load: Incandescent, fluorescent, compact fluorescent (CFL), magnetic low-voltage (MLV) and electronic low-voltage (ELV), 1/6 hp.

Top 5 Resources

-  [Sensors & Timers \(Brochure\)](#)
-  [Residential Lighting Controls \(Brochure\)](#)
-  [PIR Occupancy Sensor Switch with Manual ON/OFF, RWU600U \(Installation Instructions\)](#)
-  [Perfect Sense Sensor \(Brochure\)](#)

specifications

General Info

- Color: White
- Type: Incandescent
- Number Of Poles: 1
- Number Of Wires: 2

Listing Agencies/Third Party Information

- cU Lus: Yes
- U N SPS C: 39121502

Dimensions




- Depth (U S): 1.88"
- Height U S: 2.63"
- Width U S: 1.69"

Buy American Act Compliance

- Country of Origin: CHINA
- Buy American Act Status: No
-

resources

BROCHURE

-  Sensors & TimersPDF (578.46kb)
-  Residential Lighting ControlsPDF (264.47kb)
-  Perfect Sense SensorPDF (2.83mb)

INSTALLATION INSTRUCTIONS

-  PIR Occupancy Sensor Switch with Manual ON/OFF, RWU600UPDF (1.42mb)