

8dWwgY2xhc3M9ImhpZGUtbnV3lj4gPGxpIGNsYXNzPSJjb2wylj4gPGEgaWQ9ImN0bDA1X01haW50YXYxX2N0bDAX3JwdFJlc2lkZW50aWFsX2N0bDE0X



designed to be better.

Search

Clock Hanger Receptacles, Recessed with Smooth Wall Plate, 15A, 125V, White

S3713W
Clock Hanger Recessed Receptacle with Smooth Wall Plate 15amp 125volt White

Submit Query

Where to buy

Submit Query

Like 0

Tweet 0

0

Email Print



product gallery

Representative images shown.

AVAILABLE OPTIONS





Clock Hanger Receptacles, Recessed with Smooth Wall Plate, 15A, 125V, Black



Clock Hanger Receptacles, Recessed with Smooth Wall Plate, 15A, 125V, Ivory



Clock Hanger Receptacles, Recessed with Smooth Wall Plate, 15A, 125V, Light Almond

- SPECIFICATIONS

features & benefits

- Single recessed receptacle.
- Smooth wall plate.

specifications

General Info

- Color: White
- Type: Clock Hanger
- Special Features: Clock Hanger
- Style: Decorator, Smooth

Listing Agencies/Third Party Information

- CSA Listing Info: No
- CUL Listing No: No
- cU Lus: Yes
- cU Rus: No
- Federal Spec: No
- UL Listing No: No
- U N SPS C: 39121406
- U R: No

Dimensions

- Depth (U S): 1.878"
- Height U S: 4.478"
- Width U S: 2.74"

Technical Information

- Amps: 15 Amp
- Volts: 125V
- Volts A C: 125
- Grade Type: specification

Buy American Act Compliance

- Country of Origin: MEXICO
- Buy American Act Status: Trade Agreement Act Compliant
-

