

I9ycHRDb21tZXJjaWFsU3VibWVudV9jdGwwM19obFZpZXdMaW5rliBjbGFzc0idmldy1tb3JlliBocmVmPSlvZWxlY3RyaWNhbC13aXJpbmctZGV2aWNlcy9lbC



designed to be better.

Search

Clock Hanger Receptacles, Recessed with Stainless Steel Wall Plate, 15A, 125V

S3733SS

Clock Hanger Receptacles, Recessed with Stainless Steel Wall Plate, 15A, 125V

Submit Query

Where to buy

Submit Query

Like 0

Tweet 0

0

Email Print



product gallery

Representative images shown.

- SPECIFICATIONS

features & benefits

- Single recessed receptacle.
- Stainless steel wall plate.

specifications

General Info

- Type: Clock Hanger
- Special Features: Clock Hanger
- Style: Decorator

Listing Agencies/Third Party Information

- CSA Listing Info: No
- CUL Listing No: No
- cU Lus: No
- cU Rus: No
- Federal Spec: No
- UL Listing No: Yes
- U N SPS C: 39121406
- U R: No

Dimensions

- Depth (U S): 1.878"
- Height U S: 4.478"
- Width U S: 2.74"

Technical Information

- Amps: 15 Amp
- Material: Stainless Steel
- Volts: 125V
- Volts A C: 125
- Grade Type: specification

Buy American Act Compliance

- Country of Origin: UNITED STATES OF AMERICA
- Buy American Act Status: Buy American Act Compliant
-

