

yYz0iL34vbWVkaWEvMjgyMTFFM0E2NEVFNDYzRjk1QzdBQzNGQTNGOTIFRTkuYXNoeClgYWw0PSJMaWdodGluZyBDb250cm9sIFN5c3RlbnRlHdp



designed to be better.

 Search

## Blank Plates -- Box Mounted, Two Gang, 302 Stainless Steel

SS23

Smooth Metal Wall Plate 2gang Blank Box Mounted 302 Stainless Steel

Where to buy 


0




Representative image shown.

- SPECIFICATIONS
- RESOURCES

### features & benefits

- Type 302 Stainless Steel, non-magnetic: .032" nominal thickness.
- Brushed finish.
- This alloy contains 18% chromium and 8% nickel for superior resistance to corrosion.
- Recommended for use in food processing plants, dairies, chemical plants, and other industrial, institutional, and commercial applications where corrosive atmospheres exist.
- Constructed of corrosion-resistant stainless steel, brass, aluminum, chrome, brushed bronze, or galvanized steel.
- Standard, Jumbo, and Tandem plates available, as well as special Panel plates up to 5-gangs high and 10-gangs wide.
- Packaged in protective film, with finish-matching screws.
- Variety of special plated finishes.
- Paintable to match plastic plates.
- Can be silk-screened or engraved, and custom punched with over 300 opening styles.

### Top 5 Resources

Stainless Steel Wall Plates, SF2502R1 (Cutsheet)

### specifications

#### General Info

- Size: Standard
- Type: Box Mount
- Style: Blank Plate

#### Listing Agencies/Third Party Information

- CSA Listing Info: Yes
- CUL Listing No: No
- cU Lus: No
- cU Rus: No
- Federal Spec: No
- UL Listing No: Yes
- U N SPS C: 39121704
- U R: No

#### Dimensions

- Weight: 0.21438

#### Technical Information


- Material: 302 Stainless Steel
- Capacity: 2-gang

#### Buy American Act Compliance

- Country of Origin: UNITED STATES OF AMERICA
- Buy American Act Status: Buy American Act Compliant



**resources**  
**CUTSHEET**

 [Stainless Steel Wall Plates, SF2502R1PDF \(367.16kb\)](#)